


Number of contacts

6-64



Male header with wrap posts

Identification	No. of contacts	Part No.					
		Without levers		With short levers		With long levers	
Male header with angled wrap posts Length: 15 mm □ 0.6 mm	6	09 18 506	└ 926*	09 18 506	└ 916*	09 18 506	└ 906*
	10	09 18 510	└ 926*	09 18 510	└ 916*	09 18 510	└ 906*
	14	09 18 514	└ 926*	09 18 514	└ 916*	09 18 514	└ 906*
	16	09 18 516	└ 926*	09 18 516	└ 916*	09 18 516	└ 906*
	20	09 18 520	└ 926*	09 18 520	└ 916*	09 18 520	└ 906*
	24	09 18 524	└ 926*	09 18 524	└ 916*	09 18 524	└ 906*
	26	09 18 526	└ 926*	09 18 526	└ 916*	09 18 526	└ 906*
	30	09 18 530	└ 926*	09 18 530	└ 916*	09 18 530	└ 906*
	34	09 18 534	└ 926*	09 18 534	└ 916*	09 18 534	└ 906*
	40	09 18 540	└ 926*	09 18 540	└ 916*	09 18 540	└ 906*
	50	09 18 550	└ 926*	09 18 550	└ 916*	09 18 550	└ 906*
	60	09 18 560	└ 926*	09 18 560	└ 916*	09 18 560	└ 906*
	64	09 18 564	└ 926*	09 18 564	└ 916*	09 18 564	└ 906*
Male header with straight wrap posts Length: 15 mm □ 0.6 mm	6	09 18 506	└ 927*	09 18 506	└ 917*	09 18 506	└ 907*
	10	09 18 510	└ 927*	09 18 510	└ 917*	09 18 510	└ 907*
	14	09 18 514	└ 927*	09 18 514	└ 917*	09 18 514	└ 907*
	16	09 18 516	└ 927*	09 18 516	└ 917*	09 18 516	└ 907*
	20	09 18 520	└ 927*	09 18 520	└ 917*	09 18 520	└ 907*
	24	09 18 524	└ 927*	09 18 524	└ 917*	09 18 524	└ 907*
	26	09 18 526	└ 927*	09 18 526	└ 917*	09 18 526	└ 907*
	30	09 18 530	└ 927*	09 18 530	└ 917*	09 18 530	└ 907*
	34	09 18 534	└ 927*	09 18 534	└ 917*	09 18 534	└ 907*
	40	09 18 540	└ 927*	09 18 540	└ 917*	09 18 540	└ 907*
	50	09 18 550	└ 927*	09 18 550	└ 917*	09 18 550	└ 907*
	60	09 18 560	└ 927*	09 18 560	└ 917*	09 18 560	└ 907*
	64	09 18 564	└ 927*	09 18 564	└ 917*	09 18 564	└ 907*

* Not normally kept in stock
For accessories see page 08.22
For dimensions see page 08.21

For performance level 3 please specify digit
For performance level 2 please specify digit
S4 = 0.76 µm (30 µinch) Au or PdNi equivalent

