



Wiha Vinyl Grip Pliers & Cutters

Retaining Ring Pliers - Internal



326 Straight Internal Retaining Ring Pliers DIN ISO 5256

Shape C, straight tips. Die forged cylindrical precision formed. Chrome-vanadium special tool steel. For inserting & removing internal retaining rings.

Item		↔	↔	⊙	⊙	● Tip	⊞	↩
No.		mm	Inch	Inch	mm	Inch/mm	Pkg.	wt.
326 81	Z330J0001	139	5.5	5/16-1/2	8-13	.035/.9	1	.19
326 82	Z330J1001	140	5.5	1/2-1	12-25	.050/1.3	1	.19
326 83	Z330J2001	180	7.0	3/4-2 3/8	19-60	.070/1.5	1	.42
326 84	Z330J3001	225	8.9	1 1/2-4	40-100	.090/2.3	1	.53

90° Angle Retaining Ring Pliers - Internal



326 90° Angle Internal Retaining Ring Pliers DIN ISO 5254

Shape D, 90° angled tips. Die forged cylindrical precision formed. CV Special tool steel. For inserting & removing internal retaining rings. Soft vinyl grips.

Item		↔	↔	⊙	⊙	● Tip	⊞	↩
No.		mm	Inch	Inch	mm	Inch/mm	Pkg.	wt.
326 85	Z331J0101	139	5.5	5/16-1/2	8-13	.035/.9	1	.19
326 86	Z331J1101	140	5.5	1/2-1	12-25	.050/1.3	1	.19
326 87	Z331J2101	180	7.0	3/4-2 3/8	19-60	.070/1.5	1	.42
326 88	Z331J3101	225	8.9	1 1/2-4	40-100	.090/2.3	1	.53

Retaining Ring Pliers - External



326 Straight External Retaining Ring Pliers DIN ISO 5254

Shape A, straight tips. Die forged cylindrical precision formed. CV special tool steel. For fitting & removing external retaining rings. Soft vinyl grips.

Item		↔	↔	⊙	⊙	● Tip	⊞	↩
No.		mm	Inch	Inch	mm	Inch/mm	Pkg.	wt.
326 89	Z340A0001	139	5.5	1/8-3/8	3-10	.035/.9	1	.19
326 90	Z340A1001	140	5.5	3/8-1	10-25	.050/1.3	1	.19
326 91	Z340A2001	180	7.0	3/4-2 3/8	19-60	.070/1.5	1	.42
326 92	Z340A3001	225	8.9	1 1/2-4	40-100	.090/2.3	1	.53

90° Angle Retaining Ring Pliers - External



326 90° Angled External Retaining Ring Pliers DIN ISO 5254

Shape B, 90° angled tips. Die forged cylindrical precision formed. CV special tool steel. For fitting & removing external retaining rings. Soft vinyl grips.

Item		↔	↔	⊙	⊙	● Tip	⊞	↩
No.		mm	Inch	Inch	mm	Inch/mm	Pkg.	wt.
326 94	Z341A0101	139	5.5	1/8-3/8	3-10	.035/.9	1	.19
326 95	Z341A1101	140	5.5	3/8-1	10-25	.050/1.3	1	.19
326 96	Z341A2101	180	7.0	3/4-2 3/8	19-60	.070/1.5	1	.42
326 97	Z341A3101	225	8.9	1 1/2-4	40-100	.090/2.3	1	.53