


► Sleeving clamps

Sleeving clamps

	For wire Ø mm	Ø B (3 positions) mm	Ø A mm	L mm	I mm	H mm	ΔΔ g
985763	1,25 → 4,5	12 16 24	3,5	140	23	52	165
985764	1,75 → 9	13 18 24	4,5	140	30	56	165
985765	3 → 15	14 18 25	5,0	140	40	66	165
640171	10 → 28	19,5 22,5 30	10,0	150	56	82	149




► Pliers for plastic cable-ties

Pliers for plastic cable-ties

455B

- For all tie widths 2.4 to 9 mm.
- Strong, simple tools with good demultiplication.
- Long stroke for fast action.
- Tails cut separately to desired length.
- Replaceable blade and spring.

 $\Delta\Delta : 310 \text{ q.}$ 

Automatic pliers for plastic cable-ties

986075

- For cable tie widths 2.2 to 4.8 mm.

 $\Delta\Delta\Delta : 290 \text{ g.}$ 

▶ Plastic ties

455C Plastic ties

- Self-locking head.
- High-strength.
- Two types :
 - nylon 6.6 for indoor use.
 - polyamide 12 for outdoor use.

455.C = Ties.

455.A = Tie.

	Ties kg max	Ties l x L mm	Ø max mm	Quantity per pack	Material	ΔΔ g
455.C1	18	2,5x100	22	250	Nylon 6.6	85
455.C2	25	3,4x145	40	250	Nylon 6.6	155
455.C3	35	4,8x185	50	100	Nylon 6.6	126
455.C11	40	9,0x183	45	50	Polyamide 12	145
455.C12	48	9,0x265	70	50	Polyamide 12	180
455.C13	48	9,0x355	95	50	Polyamide 12	235
455.A1	-	20x20x6	-	50	Nylon 6.6	26
455.A2	-	21x10x4	-	50	Nylon 6.6	48

