




TECHNICAL SPECIFICATIONS


Material:	UL Recognised Plastic Material
Plating:	Nickel over Copper
Operating Temperature:	-55°C to +110°C
Cable Entry:	Side and Top (L) Side Only (S) Top Only (T)
Thumbscrews:	UNC 4-40 (Standard) M2,5 or M3 on request
Cable O.D:	Up to 11,5mm
Accessories:	See page 190-194
Assembly Instruction:	See page 198



L: Top & Side Entry



S: Side Entry Only



T: Top Entry Only

Size DSSK-T/P	Dim A	Dim B	Dim B	DimC
9-way	31,5	40,0	43,0*	15,0
15-way	40,0	40,0	-	15,0
25-way	53,5	43,0	-	15,0
37-way	71,3	40,0	-	15,0

* Top only

Features:

- Available in sizes 9-15-25-37
- Suitable for any common Sub-D connector
- Quick-snap locking system
- Re-openable
- Company logo available upon request
- Also available in Unshielded Version, See page 8
- Recyclable

Ordering information:

Size:	P/N - Kitted:	Product Code:	L
9-way	6260-0106-01	DSSK-M-09-L-K	
15-way	6260-0106-02	DSSK-M-15-L-K	
25-way	6260-0106-03	DSSK-M-25-L-K	

Size:	P/N - Kitted:	Product Code:	S
9-way	6260-0106-11	DSSK-M-09-S-K	
15-way	6260-0106-12	DSSK-M-15-S-K	
25-way	6260-0106-13	DSSK-M-25-S-K	
37-way	6260-0106-14	DSSK-M-37-S-K	

Size:	P/N - Kitted:	Product Code:	T
9-way	6260-0106-21	DSSK-M-09-T-K	
15-way	6260-0106-22	DSSK-M-15-T-K	
25-way	6260-0106-23	DSSK-M-25-T-K	

Size:	P/N - BULK:	Product Code:	L
9-way	6261-0106-01	DSSK-M-09-L	
15-way	6261-0106-02	DSSK-M-15-L	
25-way	6261-0106-03	DSSK-M-25-L	

Size:	P/N - BULK:	Product Code:	S
9-way	6261-0106-11	DSSK-M-09-S	
15-way	6261-0106-12	DSSK-M-15-S	
25-way	6261-0106-13	DSSK-M-25-S	
37-way	6261-0106-14	DSSK-M-37-S	

Size:	P/N - BULK:	Product Code:	T
9-way	6261-0106-21	DSSK-M-09-T	
15-way	6261-0106-22	DSSK-M-15-T	
25-way	6261-0106-23	DSSK-M-25-T	