

D

C

B



A

D


C

B

A



ASSEMBLED VIEW



- 1 BRACKET: STAINLESS STEEL PER QQ-S-766.
U BOLT: STAINLESS STEEL PER ASTM-A-582.
WIRE GUIDE & HEX NUT: CARBON STEEL.
PROTECTIVE SLEEVE: POLYVINYL CHLORIDE.
- 2 U BOLT: PASSIVATED.
WIRE GUIDE: 5.08um[.000200] MIN NICKEL PLATE.
HEX NUT: ZINC PLATED PER ASTM-B-633.
- 3 MAX CLAMP AREA = 225.81 SQ mm [.350 SQ IN]

SUPERSEDED BY 201224-7	201224-7
	201224-1
PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.REIFSNYDER 06 SEP 95	 Tyco Electronics Corporation Harrisburg, PA 17105-3608					
DIMENSIONS: mm [INCHES]		CHK R.STONE 15 SEP 95	NAME CLAMP KIT, UNASSEMBLED, 34 PLACE, MINIATURE RECTANGULAR, STRAIN RELIEF, M SERIES					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD G.STEINHAUER 03 OCT 95						
		PRODUCT SPEC						
		APPLICATION SPEC						
MATERIAL	FINISH	WEIGHT	—	SIZE A2	CAGE CODE 00779	DRAWING NO C-201224	RESTRICTED TO —	
		CUSTOMER DRAWING				SCALE 2:1	SHEET 1 of 1	REV V