



- 1 USE WITH PRO-CRIMPER II
- 2 SEE SEPERATE RESTRICTED CUSTOMER DRAWING WITH THIS PART NUMBER.
3. USE INSTRUCTION SHEET 9781



RECOMMENDED STRIP LENGTH

OBSOLETE OBSOLETE SUPSD BY 413588-3	AT&T 735	58174-1	39.88 [1.570]	3-328666-3	221200-9	413947-2	221402-7
	-	-	-	-	-	-	221402-6
	BELDEN 8281, 9231 AND WECO 728	220189-7	41.78 [1.645]	1-50427-6	2-221200-5	413947-3	221402-5
	BELDEN 9145	58085-1	39.88 [1.570]	50428-2	2-221200-5	413947-6	221402-4
	BELDEN 8218	58174-1	39.88 [1.570]	2-329461-7	221200-9	413947-2	221402-3
	RG-59/U, 59A/U, 59B/U	58085-1	39.88 [1.570]	50428-2	221200-3	413947-6	221402-2
	BELDEN 9248 & MADISON W/18AWG C/C	58086-1	39.88 [1.570]	50427-6	3-221200-2	413947-5	221402-1
	CABLE	DIE SET	A	3 FERRULE QTY=1	2 CONTACT QTY=1	1 PLUG ASSEMBLY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING DISPOSITION ORIGINATOR SHOULD BE CONTACTED FOR THE LATEST VERSION.		DWN J. LIPPERT OSJANG7	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm[INCHES]		CHK M. PHILLIPS OSJANG7	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. PHILLIPS OSJANG7	PRODUCT SPEC	
0 PLG ±		108-12020		
1 PLG ±		APPLICATION SPEC		
2 PLG ±0.41[.016]		SIZE		
3 PLG ±		CAGE CODE		
4 PLG ±		DRAWING NO		
ANGLES ±		RESTRICTED TO		
FINISH		WEIGHT		
MATERIAL		CUSTOMER DRAWING		
		SCALE 4:1 SHEET 1 OF 1 REV L		