

Housing - HC-HV 10/16-TMQ-76/O1M25S - 1604943

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON sleeve housing HV10/16, with double locking latch, height 76 mm, with support 1x M25, lateral conductor exit

Key commercial data

Packing unit	1 PCE
GTIN	 4 017918 883164
Weight per Piece (excluding packing)	450.8 GRM
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	76 mm
Width	43 mm
Length	120 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-HV10/16
Design	HV10/16
Housing type	Sleeve housings
Locking type	With double locking latch
No. of cable exits	1
Cable exit	Lateral
Type of the screw connection	1x M25
Housing material	Aluminum die-cast

Housing - HC-HV 10/16-TMQ-76/O1M25S - 1604943

Technical data

General

Housing surface material	Powder-coated, gray
Material lock	High-grade steel
Material grip body interlock	PA-GF

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

GOST

Ex Approvals

Housing - HC-HV 10/16-TMQ-76/O1M25S - 1604943

Approvals

Approvals submitted

Approval details

GOST 