




1. WIRE RANGE: 0.3 - 0.9 MM² (22 - 18 AWG)




SECTION A-A



SECTION B-B

2.29	.090	2.67	.105	10.21	.402	-	-
0.32	.013	2.41	.095	6.48	.255	11.05	.435
0.13	.005	2.36	.093	3.05	.120	10.36	.408
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE



MINI	350015-2
STANDARD	350015-1
APPLICATOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
0.32 PH BRZ

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±-

FINISH
PRE TIN

DWN
T. BECK
6-17-97

CHK
R. SWING
6-17-97

APVD
A. BEDDICK
8-22-97

PRODUCT SPEC
108-1025

APPLICATION SPEC
114-1008

WEIGHT
-

CUSTOMER DRAWING

NAME
AMP Incorporated
Harrisburg, PA 17105-3608

RECEPTACLE, .093 DIAMETER,
22-18 AWG, P.C. CONTACT

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-350015

RESTRICTED TO
-

SCALE
10:1

SHEET
1

OF
1

REV
G