




LOC		DIST		REVISIONS			
P	U/R	DESCRIPTION		DATE	DWN	APVD	
L		003B-0397-03		12MAY03	TK	GS	



RECOMMENDED LAYOUT

- 1 NYLON, UL 94-VO RATED, RED.
- 2 PHOSPHOR BRONZE.
- 3 3.81µm [.000150] MIN TIN-LEAD OVER 1.27µm [.000050] MIN NICKEL.
- 4 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81µm [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 5 3.81µm [.000150] MIN TIN OVER 1.27µm [.000050] MIN NICKEL.

5	YES	207530-7
4	NO	207530-4
4	YES	207530-3
3	NO	207530-2
3	YES	207530-1
CONTACT FINISH		MOUNTING TABS
		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE	03/19/92		 Tyco Electronics Corporation Harrisburg, Pa			
		DRW	L SIPE					
DIMENSIONS:		CHK	R STONE		NAME			
INCHES		APVD	A TRAVIS					
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SOCKET HEADER ASSEMBLY, 18 POSITION, METRIMATE			
		0 P/LC ± —		108-10033				
		1 P/LC ± —		APPLICATION SPEC				
		2 P/LC ± 0.25 [010]		—				
3 P/LC ± —		WEIGHT		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
4 P/LC ± —					A2	00779	©-207530	—
5 P/LC ± —								
ANGLES								
FINISH								
MATERIAL								
HOUSING: 		CONTACT: SEE TABLE		CUSTOMER DRAWING				
				SCALE 4:1 SHEET 1 of 1 REV L				