








SECTION Z-Z




SECTION Y-Y



RECOMMENDED PCB LAYOUT
TOLERANCE:0.03



SECTION X-X



NOTES:

1. PRODUCT SPECIFICATION: PS-105190-001
2. PACKAGE DRAWING: PK-105190-001
3. COPLANARITY:0.08mm MAX.
4. PAKAGING: TAPE&REEL

3	SHELL	PHOSPHOR BRONZE ALLOY	2.0 MICRO MIN. NICKEL UNDERPLATING OVERALL 0.8-2.8 MICRON BRIGHT TIN PLATING OVERALL	T=0.12mm
2	TERMINAL	PHOSPHOR BRONZE ALLOY	2.0 MICRO MIN. NICKEL UNDERPLATING OVERALL GOLD PLATING 0.3 MICRON Min. ON CONTACT AREA, GOLD FLASH PLATING ON SOLDER AREA.	T=0.12mm
1	HOUSING	HIGH-TEM THERMAL PLASTIC	BLACK	UL94 V-0
NO.	PART NAME	MATERIAL	SURFACE FINISH	REMARK

RELEASED
EC NO: SH2013-0196
2012/12/18
DRW:WJHUO
CHKD:
APPR:AYIN
2013/01/08

QUALITY SYMBOLS
F=0
E=0
E=0

GENERAL TOLERANCES (UNLESS SPECIFIED)	
	mm INCH
4 PLACES	± --- ± ---
3 PLACES	± --- ± ---
2 PLACES	± 0.15 ± ---
1 PLACE	± 0.20 ± ---
0 PLACE	± --- ± ---
ANGULAR ± 3 °	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
MM ONLY	
DRAWN BY	DATE
WJHUO	2012/12/18
CHECKED BY	DATE
WJHUO	2012/12/18
APPROVED BY	DATE
AYIN	2013/01/08

SCALE 5:1	DESIGN UNITS METRIC		THIRD ANGLE PROJECTION
TITLE			
SD DRAWING SMIA 75 CAMERA SOCKET TOP MOUNT			
molex			
DOCUMENT NO. SD-105190-001			SHEET NO. 1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			