



REV.	DATE	DESCRIPTION
NC	03/06/00	INITIAL RELEASE




RECOMMENDED
CABLE STRIPPING DIM'S





RECOMMENDED
MOUNTING HOLE

6 HEX NUT



10-32UNF-2A

6 HEX



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .178"

	DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	APPROVALS	DATE	 Connector Corporation					
1	BODY	BRASS	NICKEL	DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	DRAWN	G.R.S.					03/06/00	
2	FERRULE	COPPER	NICKEL		CHECKED							
3	LOCK WASHER	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	ISSUED		TITLE					
4	HEX NUT	BRASS	NICKEL				BULKHEAD CABLE TERMINATION (FOR RG-180B/U, 195/U CABLE)					
5							SIZE	FSCM NO.	DWG. NO.	REV.		
6							A	99001	142276.DWG	NC		
7												
8				DO NOT SCALE DRAWING			SCALE	NA	PART NO.	142276	SHEET	1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142276](#)