




(1,27 mm) .050"

CFT, CFS SERIES

COMPACT FLASH TERMINALS & SOCKETS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?CFT or www.samtec.com?CFS

Insulator Material:
Black Liquid Crystal Polymer

Terminal Material (CFT):
Phosphor Bronze

Contact Material (CFS):
BeCu

Plating:
Sn or Au over 50µ" (1,27 µm) Ni

Operating Temp Range:
CFT = -55°C to +105°C Tin
CFT = -55°C to +125°C Gold
CFS = -55°C to +125°C

Contact Resistance (CFS):
10 mΩ

Insertion Depth (CFS):
(3,05 mm) .120" min

Insertion Force (CFS):
(Single contact only)

3.3 oz (0,92 N) avg.

Withdrawal Force (CFS):
(Single contact only)

2.5 oz (0,70 N) avg.

Lead-Free Solderable:
Yes

SMT Lead Coplanarity:
CFT = (0,15 mm) .006" max


CFS = (0,10 mm) .004" max

RoHS Compliant:
Yes

CFT - 125 - LEAD STYLE - PLATING OPTION - D - RA - CARD LENGTH - SL

Mates with:
CFS

Specify
LEAD
STYLE
from chart



-L
= 10µ" (0,25 µm) Gold on post,
Matte Tin on tail


-S
= 30µ" (0,76 µm) Gold on post,
Matte Tin on tail

-01
= (25,40 mm) 1.00"
Card Length


-02
= (50,80 mm) 2.00"
Card Length

LEAD STYLE	Y
-01	(6,35) .250
-02	(8,89) .350

POSITION NUMBER	C (POST)
(3,50) .138	(3,50) .138
(5,00) .197	(5,00) .197
(4,25) .167	(4,25) .167



APPLICATIONS



RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594



CFS - 1 - NO. PINS PER ROW - CARD THICKNESS - PLATING OPTION - D

Mates with:
CFT


25

-01
= (0,80 mm) .031" thick board

-02
= (1,60 mm) .062" thick board

-L
= 10µ" (0,25 µm) Gold on contact,
Matte Tin on tail

-S
= 30µ" (0,76 µm) Gold on contact,
Matte Tin on tail



CARD THICKNESS	A	B	C
-01	(1,02) .040	(1,79) .070	(3,12) .123
-02	(1,70) .067	(2,46) .097	(2,77) .109

Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685