


REV.	DATE	DESCRIPTION
NC	06/03/96	INITIAL RELEASE
A	10/01/06	UPDATE DRAWING FORMAT
B	10/19/06	REVISE BODY PLATING TO NEXCOTE



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 ± 0.007" .315 – 1.180 ± 0.015" 1.180 – 4.724 ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
7						DRAWN	G.R.S.						10/19/06
6						CHECKED			PART DESCRIPTION N "T" ADAPTER JACK–PLUG–JACK				
5						ISSUED							
4						SHEET	1 OF 1		PART NO. 172125				
3	CONTACT PIN	BRASS	GOLD	3									
2	INSULATOR	TEFLON	NATURAL	1				DWG. NO. 172125.DWG					
1	BODY	BRASS	NEXCOTE	1									
DESCRIPTION MATERIAL FINISH QTY					CAD FILE C:/172/172125.DWG			REV. B	SIZE A	SCALE NA			