




TRADE PRICE LIST

January 1998

BUCKET PUMPS, AIR OPERATED LUBRICATORS

Prices exclusive of VAT




PORTABLE GREASE LUBRICATION UNITS
For highpressure greasing direct to bearing.
Output: 2.500 per stroke
Pressure: Max 4000psi (260 bar)

TRADE
PRICE
EACH

Heavy Duty Bucket Pump for 12.5kg grease keg.
Kit includes: pump with cast-alloy head, steel drum lid, follower plate, H.P. rubber hose (2m long), hand-stem with shut-off valve and 4 jaw hydraulic connector.

10092-125/HC5

As above, but for 20kg grease keg **10092-200/HC5**
(To suit Taper Keg dia. 305/280mm)




Standard Bucket Pump for 12.5kg Grease Keg.
Kit includes: pump, steel drum lid, nylon hose (1.7m long), hand-stem with hydraulic connector.

55-1172

As above, but for 20kg grease keg **55-1230**
(To suit Taper Keg dia. 305/280mm)

Accessories and Options

Field Gun for remote high pressure greasing -
filled via. grease nipple in head.
Output: 0.5cc per stroke Pressure: Max. 7500psi (500 bar)
555/N



Follower Plate for 12.5Kg Keg	55-9129
Follower Plate for 20 Kg Keg	55-9130
Spare Keg 12.5Kg	10622
Spare Hose Assembly - Nylon	10092-002
Spare Hose Assembly - Rubber	10092-003
Shut-off Valve - 1/8" BSP	91-1011

For details of Grease Gun Connectors, refer to our
"Grease Guns and Accessories" Price List.

LUMATIC [GA] Limited. Hastings, E. Sussex TN34 1YS

Telephone 01424 429926

Fax 01424 429926