

Search Results

Evaluate

- FAQ's

Design a Solution

- Catalog Cut Sheet
- PDF-CMRPSH15 Pro
- Part Drawings
- DXF-Metered Powe ..
- DWG-Metered Powe ..
- PDF-Metered Powe ..
- Specification Sheets
- PDF-Power Strips

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-Panduit POU ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) [Search Tips](#) 

☒ **Text Search: 'RPSH163C13TL6M'**

Your search criteria matched only one product, shown below

RPSH163C13TL6M



Rack Mount Power Outlet Units

- Mounting brackets and screws included

▪ Part Number	RPSH163C13TL6M
▪ RoHS Compliance Status	Compliant
▪ Part Description	Horizontal power strip 30 A, 208V, sixteen IEC C-13 receptacles, four 15 A thermal breakers, red LED current monitor, and 10' power cord with NEMA L6-30P twist lock plug. UL and c-UL Listed. Dimensions: 3.5"H x 19"W x 1.6"D (88mm x 483mm x 41mm)
▪ Product Type	Horizontal Power Outlet Unit
▪ Color	Black
▪ Depth (In.)	1.6
▪ Depth (mm)	41
▪ Height (In.)	3.5
▪ Height (mm)	88
▪ Width (In.)	19
▪ Width (mm)	483
▪ CE Compliant	No
▪ No. of Rack Spaces	2
▪ Plug Type	NEMA L6-30P
▪ Pricing Description	Horizontal 30 AMP,16 EIC Outlet w/ Power Meter
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ Voltage	208V
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.