


W67-X2Q12-15 Product Details



W67-X2Q12-15

TE Internal Number: 5-1393252-6

 **Active**

Magnetic Circuit Breakers

 Converted to EU RoHS but not ELV Compliant
(Statement of Compliance)

Product Highlights:

- Magnetic Circuit Breaker
- Series/Mounting Option = W6 (6-32 Mtg. Threads)
- Actuator Style = Toggle
- Circuit Breaker Size = 50.8 mm
- 1 Poles

Documentation & Additional Information	
Product Drawings: • None Available Catalog Pages/Data Sheets: • W6/W9 Magnetic Hydraulic Circuit Breaker (PDF, English) Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: (CAD Format & Compression Information) • 2D Drawing (DXF, Version 1106) • 3D Model (IGES, Version 1106) • 3D Model (STEP, Version 1106)	Related Products: • Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Circuit Breaker Type = Magnetic • Actuator Style = Toggle • Termination Type = 6.35 [.250] Straight Quick Connect Tab Mechanical Attachment: • Series/Mounting Option = W6 (6-32 Mtg. Threads) Electrical Characteristics: • Current Rating (A) = 15 • Operating Voltage, Max. = 415/240 VAC • Interrupt Capacity = 5,000 A @ 277 VAC Dimensions: • Circuit Breaker Size (mm [in]) = 50.8 [2]	Contact Features: • Number of Poles = 1 • Toggle Color = White • Trip Time at 200% = 2.2 to 20 Seconds Configuration Features: • Circuit Function = Series Trip Industry Standards: • RoHS/ELV Compliance = RoHS/Not ELV Compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Converted to comply with RoHS not ELV directives Other: • Brand = Potter & Brumfield