

/auto2/new/u.099-0097 customer/s.c-175266

PRINT DIST





単位: mm DIMENSIONS IN MM. DO NOT SCALE PRINT

METRIC

三角度 (3rd ANGLE PROJECTION)

NUMBER



C-175266



NOTE ,
1. SELECTIVE GOLD
2. APPLICATION SPEC NO. 114-5159
3. THE STAMP DISCERN GOLD
PLATING FROM TIN PLATING
4. SELECTIVE TIN

-2, AS SHOWN

-5, AS SHOWN
-7, AS SHOWN



L	REVISED (FJ00-1220-99)	KS	MT	15JUL 99
K	改訂 (FJ00-0577-98)	TK	NS	25MAR 98
J	改訂 (FJ00-1031-97)	HY	NS	29AUG 97
H	改訂 (FJ00-1905-95)	TS	KA	2/22 95
G	改訂 (FJ00-1472-94)	TS	KA	2/22 95
F	改訂 (FJ00-0975-94)	TS	KO	8/2 94
E	改訂 (FJ00-0097-94)	TS	KO	6/14 94
D	改訂 (FJ00-0153-94)	TK	MT	4/3 94
C	改訂 FJ00-0051-93	YK	KO	2/4 93
B	改訂 J-0212	KO	SI	7/8 91
A	再作成	KO	SI	4/25 91
LTR	変更 (REVISION RECORD)	DR	CHK	DATE

0.76μm以上	—	部分金めつき (SELECTIVE GOLD) バレルすずめつき (SELECTIVE TIN)	175266-7
0.76μm以上	—	部分金めつき (SELECTIVE GOLD)	175266-5
0.38μm以上	179418-2	部分金めつき (SELECTIVE GOLD)	175266-2
金めつき厚 (GOLD PLATING THICKNESS)	バラ端子型番 (LOOSE PIECE CONTACT P/N)	仕上げ (FINISH)	AMP型番 (PART NUMBER)
Copyright ©1990年 AMP (Japan), LTD. ALL RIGHTS RESERVED.		AMP 日本エー・エム・ピー株式会社 Tokyo, Japan	
絶縁電線断面積 (WIRE RANGE)	絶縁外径 (INSULATION DIA.)	名称 (NAME) .040〇〇 SERIES S RECEPTACLE CONTACT	
0.37~0.88 mm ² (AWG #22-#18)	1.1~2.1 mmφ	.040〇〇 シリーズ S リセプタクル コンタクト	
材料 (MATERIAL)	仕上 (FINISH)	一般公差 (GENERAL TOLERANCE)	
KLF-5	SEE TABLE	10以下: ±0.2 10~30以下: ±0.25 30~100以下: ±0.3 角 度: ±3°	
DR. K. Oda 4/25'91	DE. K. Oda 4/25'91	LOD	番号 (No.)
CHK. —	APP. Schmitt 4/25'91	B J	C-175266
尺度 (SCALE)		REV.	SHEET
5-1		L	1 OF 1