


PRODUCT DATA SHEET

Type	Size	Rating	Description	Part No.
Incandescent	T5	12V 2W	T-1½ Wedgebase Lamp	924-002LF



Drawing Not To Scale
All Dimensions In mm

PHOTOMETRY DATA

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE (Hours)
	Min.	Nom.	Max.	Min.	Nom.	Max.	
12.0	148	165	182	6.0	7.5	9.0	1000

NOTES:

- 1) W2x4.6d in accordance with IEC 61-1, (BS EN 60061-1), sheet 7004-94-x.
- 2) C-2V filament shape.
- 3) Clear Glass bead.
- 4) Lamp components are lead-free
- 5) Lamp marking: VCH . X
12V2W Y to be durably printed on the bulb, where X & Y are a lot code.

Issue No.	Date	C.N. No.	Drawn	Tech	QA	Sales
2	22/11/06	-	BCW		Approved	