

4



3

2


1

| REVISIONS |     |                           |           |     |      |
|-----------|-----|---------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|           | B   | REVISED PER ECO-17-008763 | 19DEC2017 | RG  | SH   |


D



COVER HOUSING  
(2EA/KIT)



C



B

- NOTE
- MATERIAL & FINISH  
\*CONTACT;COPPER ALLOY Au PL.0.3 AND 0.76 MIN. AT CONTACT AREA AND TIN PL. AT I.D. AREA OVER Ni PL.  
\*FRONT SHELL; STEEL, Ni PL.  
\*HOUSING(BASE,FACE,COVER);  
THERMO-PLASTIC,GF,UL 94V-0. BLACK
  - APPLICABLE WIRE;PLEASE CONFIRM TO TE CONNECTIVITY ENGINEERING.

|           |       |       |      |      |      |            |    |     |             |
|-----------|-------|-------|------|------|------|------------|----|-----|-------------|
| OBSOLETED | 49.53 | 54.69 | 55.7 | 60.3 | 60.2 | 0.76u      | 39 | 80  | 3-5175677-0 |
|           | 62.23 | 67.45 | 68.4 | 73.0 | 72.9 | 0.76u      | 49 | 100 | 2-5175677-9 |
|           | 41.91 | 47.13 | 48.0 | 52.7 | 52.6 | 0.76u      | 33 | 68  | 2-5175677-8 |
|           | 30.48 | 35.70 | 36.6 | 41.3 | 41.2 | 0.76u      | 24 | 50  | 2-5175677-7 |
|           | 21.59 | 26.81 | 27.7 | 32.4 | 32.3 | 0.76u      | 17 | 36  | 2-5175677-5 |
|           | 15.24 | 20.46 | 21.4 | 26.0 | 25.9 | 0.76u      | 12 | 26  | 2-5175677-4 |
|           | 11.43 | 16.65 | 17.6 | 22.2 | 22.1 | 0.76u      | 9  | 20  | 2-5175677-2 |
|           | 7.62  | 12.84 | 13.7 | 18.4 | 18.3 | 0.76u      | 6  | 14  | 2-5175677-1 |
| OBSOLETED | 49.53 | 54.69 | 55.7 | 60.3 | 60.2 | 0.3 u      | 39 | 80  | 1-5175677-0 |
|           | 62.23 | 67.45 | 68.4 | 73.0 | 72.9 | 0.3 u      | 49 | 100 | 5175677-9   |
|           | 41.91 | 47.13 | 48.0 | 52.7 | 52.6 | 0.3 u      | 33 | 68  | 5175677-8   |
|           | 30.48 | 35.70 | 36.6 | 41.3 | 41.2 | 0.3 u      | 24 | 50  | 5175677-7   |
|           | 21.59 | 26.81 | 27.7 | 32.4 | 32.3 | 0.3 u      | 17 | 36  | 5175677-5   |
|           | 15.24 | 20.46 | 21.4 | 26.0 | 25.9 | 0.3 u      | 12 | 26  | 5175677-4   |
|           | 11.43 | 16.65 | 17.6 | 22.2 | 22.1 | 0.3 u      | 9  | 20  | 5175677-2   |
|           | 7.62  | 12.84 | 13.7 | 18.4 | 18.3 | 0.3 u      | 6  | 14  | 5175677-1   |
| A         |       | B     | C    | D    | E    | Au.PLATING | n  | POS | PART No.    |

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
一般公差

10 ≧ : ±0.2  
30 ≧ > 10 ±0.25  
100 ≧ > 30 ±0.3  
ANGLES ±3°

MATERIAL  
SEE NOTES

FINISH  
SEE NOTES

DWN 19APR05  
COREL.WANG

CHK 19APR05  
STEVEN YAO

APVD 19APR05  
I.ENOMOTO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT 0.000000

CUSTOMER DRAWING

TE Connectivity Ltd.

NAME

CHAMP .050 PLUG CONN. KIT

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-5175677

—

SCALE 2:1

SHEET 1 OF 1

REV B