

GRM0336T1E270JD01#

“ # ” indicates a package specification code.

Discontinued

General

125℃


Ultra-compact

Reflow OK

RoHS

< List of part numbers with package codes >
GRM0336T1E270JD01D , GRM0336T1E270JD01W , GRM0336T1E270JD01J

Shape



L size	0.6 ±0.03mm
W size	0.3 ±0.03mm
T size	0.3 ±0.03mm
External terminal width e	0.1 to 0.2mm
Distance between external terminals g	0.2mm min.
Size code in inch(mm)	0201 (0603)

References

Packaging	Specifications	Minimum quantity
D	φ 180mm Paper taping	15000
J	φ 330mm Paper taping	50000
W	φ 180mm Paper taping (W8P1*) * Width : 8mm, Pocket pitch : 1mm	30000

Mass (typ.)	
1 piece	0.33mg
φ 180mm Reel	118g

Specifications

Capacitance	27pF ±5%
Rated voltage	25Vdc
Temperature characteristics (complied standard)	T2H(EIA)
Temperature coefficient	-470±60ppm/℃
Temperature range of temperature characteristics	25 to 85℃
Operating temperature range	-55 to 125℃

⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ’ s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.