

Earth Ground Resistance Tester Kit

 **Includes all hardware necessary to measure earth ground**
In 3 ranges from 20 to 2000 Ω

Features:

- Large dual display with backlight
- Test Hold function for easy operation
- Automatic Zero adjustment
- AC/DC Voltage, Resistance, and Continuity
- Auto Power off
- Overrange and low battery indication
- Complete with test leads, 2 auxiliary earth bars, carrying case, protective rubber holster and six 1.5V AA batteries



Specifications

Earth Ground Resistance ranges	20 Ω 200 Ω 2000 Ω
Basic Accuracy	$\pm(2\%rdg+2d)$
Resolution	0.01 Ω 0.1 Ω /1 Ω
Test Current / Frequency	<2.5mA / 820Hz
AC Earth Voltage / Frequency	0 to 200VAC / 50 to 400Hz
Accuracy	$\pm(3\%rdg+3d)$
DC Voltage	0 to 1000V
Accuracy	$\pm(0.8\%rdg+3d)$
Resistance	0 to 200k Ω
Accuracy	$\pm(1\%rdg+2d)$
Continuity	40 Ω
Power supply	Six 1.5V 'AA' Batteries
Dimensions	7.9 x 3.6 x 2" (200 x 92 x 50mm)
Weight	1.5lbs (700g) (meter only)

Ordering Information:

- 382252.....Earth Ground Resistance Tester Kit
382252-NIST.....382252 with Calibration Traceable to NIST.
382253.....Replacement Earth Bars (2pk)
382254.....Replacement Set of Leads

