

Query about: 'GSRB'

Total 161 Records,Page:1/41

▼

 Each Page:

50Records

▼

Part Number	Plug-in unit pattern THT/SMD	Magnetism structure Open/Colse/Annular	Length (mm)	Width (mm)	Height (mm)	Inductance (? H) (L)	Impedance (?) (Z)	DCR(?) (max)	IDC(A) (max)
GSRB?0605-101M	THT	開磁	6.5	6.5	5.5	100		0.68	0.42
GSRB?0605-102M	THT	開磁	6.5	6.5	5.5	1000		7.06	0.13
GSRB?0605-121M	THT	開磁	6.5	6.5	5.5	120		0.77	0.39
GSRB?0605-151M	THT	開磁	6.5	6.5	5.5	150		0.95	0.35
GSRB?0605-181M	THT	開磁	6.5	6.5	5.5	180		1.15	0.32
GSRB?0605-220M	THT	開磁	6.5	6.5	5.5	22		0.18	0.9
GSRB?0605-221M	THT	開磁	6.5	6.5	5.5	220		1.3	0.29
GSRB?0605-270M	THT	開磁	S	6.5	5.5	27		0.21	0.81
GSRB?0605-271M	THT	開磁	6.5	6.5	5.5	270		1.55	0.26
GSRB?0605-330M	THT	開磁	6.5	6.5	5.5	33		0.27	0.74
GSRB?0605-331M	THT	開磁	6.5	6.5	5.5	330		2.18	0.23
GSRB?0605-390M	THT	開磁	6.5	6.5	5.5	39		0.29	0.68
GSRB?0605-391M	THT	開磁	6.5	6.5	5.5	390		2.47	0.21
GSRB?0605-470M	THT	開磁	6.5	6.5	5.5	47		0.34	0.62
GSRB?0605-471M	THT	開磁	6.5	6.5	5.5	470		2.92	0.2
GSRB?0605-560M	THT	開磁	6.5	6.5	5.5	56		0.42	0.57
GSRB?0605-561M	THT	開磁	6.5	6.5	5.5	560		3.97	0.18
GSRB?0605-680M	THT	開磁	6.5	6.5	5.5	68		0.48	0.51
GSRB?0605-681M	THT	開磁	6.5	6.5	5.5	680		4.57	0.16
GSRB?0605-820M	THT	開磁	6.5	6.5	5.5	82		0.55	0.47
GSRB?0605-821M	THT	開磁	6.5	6.5	5.5	820		5.28	0.15
GSRB?0606-101M	THT	開磁	6.5	6.5	6.5	100		0.43	0.59
GSRB?0606-102M	THT	開磁	6.5	6.5	6.5	1000		4.45	0.19
GSRB?0606-121M	THT	開磁	6.5	6.5	6.5	120		0.54	0.54
GSRB?0606-151M	THT	開磁	6.5	6.5	6.5	150		0.64	0.48
GSRB?0606-181M	THT	開磁	6.5	6.5	6.5	180		0.74	0.44
GSRB?0606-220M	THT	開磁	6.5	6.5	6.5	22		0.11	1.27
GSRB?0606-221M	THT	開磁	6.5	6.5	6.5	220		0.96	0.4
GSRB?0606-270M	THT	開磁	6.5	6.5	6.5	27		0.14	1.14
GSRB?0606-271M	THT	開磁	6.5	6.5	6.5	270		1.12	0.36
GSRB?0606-330M	THT	開磁	6.5	6.5	6.5	33		0.17	1.03
GSRB?0606-331M	THT	開磁	6.5	6.5	6.5	330		1.48	0.33
GSRB?0606-390M	THT	開磁	6.5	6.5	6.5	39		0.19	0.95
GSRB?0606-391M	THT	開磁	6.5	6.5	6.5	390		1.66	0.3
GSRB?0606-470M	THT	開磁	6.5	6.5	6.5	47		0.23	0.87
GSRB?0606-471M	THT	開磁	6.5	6.5	6.5	470		1.91	0.27
GSRB?0606-560M	THT	開磁	6.5	6.5	6.5	56		0.26	0.8
GSRB?0606-561M	THT	開磁	6.5	6.5	6.5	560		2.31	0.25
GSRB?0606-680M	THT	開磁	6.5	6.5	6.5	68		0.28	0.72
GSRB?0606-681M	THT	開磁	6.5	6.5	6.5	680		2.67	0.23
GSRB?0606-820M	THT	開磁	6.5	6.5	6.5	82		0.39	0.66
GSRB?0606-821M	THT	開磁	6.5	6.5	6.5	820		3.1	0.21
GSRB?0805-100M	THT	開磁	8.3	8.3	5.5	10		0.07	2.5
GSRB?0805-101M	THT	開磁	8.3	8.3	5.5	100		0.52	0.81
GSRB?0805-102M	THT	開磁	8.3	8.3	5.5	1000		5.28	0.25
GSRB?0805-103M	THT	開磁	8.3	8.3	5.5	10000		55.7	0.081
GSRB?0805-120M	THT	開磁	8.3	8.3	5.5	12		0.08	2.4
GSRB?0805-121M	THT	開磁	8.3	8.3	5.5	120		0.59	0.76
GSRB?0805-122M	THT	開磁	8.3	8.3	5.5	1200		6.03	0.23
GSRB?0805-150M	THT	開磁	8.3	8.3	5.5	15		0.09	2.1

Totals 161 Records,Page:1/41

▼

 Each Page:

50Records

▼