


Sta-Kon®



T&B Catalog Number: A115-TB
UPC Number: 78621046301
Description: Non-Insulated Fork Terminal For Wire Range 22-16 Stud Size #10, Metallic

Status: Active



WEB_USE

-T&B Product Line	-- 029
-US Cutsheet PDF Catalog Link	-- http://www-public.tnb.com/contractor/docs/stakon.pdf

Features

-	-- These non-insulated fork terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
---	--

General

-Insulation Type	-- Non-Insulated
-Terminal Series	-- A
-Material	-- Copper
-Finish	-- Electro -Tin Plated
-Color	-- Metallic
-Wire Range	-- 22-16
-Stud Size	-- #10

Dimension Information

-Stock Thickness	-- .03
-A (inches)	-- .75
-B (inches)	-- .31
-C (inches)	-- .27
-M (inches)	-- .59

Specifications

-Temperature Rating	-- 150°C
-Voltage Rating	-- 600V
-Flammability Rating	-- UL 94 V-0

Tooling

-Tool Charts	Available on Website
-Application Tools	-- WT110M, WT111M, WT112M, WT2000, ERG4002
-Recommended Tool	-- ERG4001

Packaging

-T&B Order Multiple	-- 1000
-T&B Inner Pack	-- 1000
-Package in Units	-- 10000
-Package Type	-- Bulk
-T&B Sold in UOM	-- Each
-T&B Weight Per UOM	-- 0.15 lbs. per 100
-Alternate Package Qty	-- A18-10F

Application Support

-Overview	Available on Website
-----------	----------------------

-Wire Guide Tables

Available on Website

Notes

-

-- Most terminals can be put on Mylar Tape for reel fed applications by adding the suffix M to the bulk catalog numbers.

Certifications

-RoHS Compliance

-- Yes

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com