



# Single Row Angle Adjust Tube Lighting from Inspired LED



## Mounting Options to Meet Every Need:



- Direct your light where it's most needed.
- Snap-in mounts allow for simple grab and twist adjustment.
- Powered by 12VDC source from Inspired LED:
  - Plug-in Power Supplies
  - Hard-wire Dimmable Transformer
- Available in Warm White (3000K) or Cool White (6000K).
- Each LED outputs roughly 6.5 lumens with a 120° viewing angle.
  - Rated for 100,000 hours of use.
  - No IR or UV light – safe for lighting delicate materials.
- Available in standard sizes:
  - 21 LED (9 inches)
  - 42 LED (17 inches)
- Available in custom lengths from 3.5" to 60.5"
  - Increments of roughly 1.25"
  - Call for lengths longer than 60.5"
- Manufactured in Tempe, Arizona.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Inspired LED:

[TT-3200-60-2C](#)