

Brilliance by design

Low Profile, Splashproof, Front Mounting Indicator

MODEL 253


Same features as 252 but with O-ring for sealing panel from water & dust.

FEATURES

- Panel mount in 5/16" (0.312") diameter hole
- Black anodized aluminum body
- No lens for maximum viewing angle.



Suggested mounting diameter 5/16"



HOW TO ORDER

Voltage	Model No.	Voltage	Model No.
2vdc*	253-2X	12vdc	253-12Y
5vdc	253-5X	24vdc	253-24Y
12vdc	253-12X	28vdc	253-28Y
24vdc	253-24X		
28vdc	253-28X		

Where the 'X' appears insert: 1-Red, 2-Green, 3-Yellow, 4-Amber, 5-Ultra Green, 6-Ultra Blue
 Where the 'Y' appears insert: 7-Pure White

Supplied with 6" wire leads

*external resistor required


253 444

MODEL 444

This Splashproof front mounting indicator is a low profile design with a bright LED, comes with or without a lens for neat panel appearance. Suggested 5/16" panel mounting hole. O-ring supplied to seal between the panel and indicator from dust and water. Supplied with a 6 inch wire lead. Available in a variety of colors and voltages (please specify when ordering).



Suggested mounting diameter 5/16"



FEATURES

- Splashproof
- Long Life LED
- Low power consumption
- Panel mount in 5/16" (0.312") diameter hole

NOTE:

*For Voltage/Current Specs, see page A-1.

Omit voltage/current specification to order without built-in resistor.

HOW TO ORDER

Voltage	Model No.	Voltage	Model No.
5vdc	444-5X	5vdc	444-5Y
12vdc	444-12X	12vdc	444-12Y
24vdc	444-24X	24vdc	444-24Y

Where the 'X' appears insert: 1-Red, 2-Green, 3-Yellow, 4-Amber, 5-Ultra Green, 6-Ultra Blue

Where the 'Y' appears insert: 7-Pure White

Supplied with 6" wire leads

Brilliance by design

LED Voltage & Current Options

VOLTS	CURRENT IN MILLIAMPS
5 VDC	10, 15, 20, 25 (MA)
12 VDC	10, 20 (MA)
24 VDC	10, 20 (MA)
28 VDC	10, 20 (MA)

Neon Lamp Electrical Specifications

(Used in 502, 857, 858, 859 and 862 Models)

LAMP with RESISTOR	VOLTS A.C. or D.C.	AMPS NOMINAL	WATTS NOMINAL	LIFE	RESISTOR
A1B	105-125	.03	1/25	25,000	220K
A1C	105-125	1.2	1/7	25,000	47K
A9A (NE-2E)	105-125	0.7	1/12	25,000	100K
C2A (NE-2H)	105-125	1.9	1/4	25,000	30K

NOTE: A1C and NE-2H are high brightness. Other lamps available. Life figures for A.C. - Life at D.C. 1/2 A.C. (Approx.). 862 Series cannot be supplied with resistor.

IMPORTANT: The lamps shown represent the most popular types normally requested.
 MANY OTHER LAMPS ARE AVAILABLE - PLEASE CONTACT FACTORY.

Hot Stamping Information

The chart below designates type sizes available for hot stamping.
 Size of lens determines size of type that can be used.

TYPE	ACTUAL SIZE	
	WIDTH	HEIGHT
2 pt	.050	.060
6 pt	.060	.080
8 pt	.080	.110
10 pt	.090	.120
12 pt	.110	.160

NOTE: For other size type, contact factory.