

GHC-121000

GENERAL FEATURES

- Single Stage Float charging
- Semi-Switching Technology
- Regulated charge voltage
- Semi-constant current
- Fully Automatic Operation
- Compact and Light weight
- Overload protected (auto recovery)
- Reverse Polarity Protection
- UL/CUL Listed



12 Volt 1 Amp

INPUT

Input	120 VAC
Frequency	60Hz
Protection	Internal Primary
Isolation	Input-Output 3000VAC
	Input-Case 2500 VAC
	Output-Case 500VAC
Safety	UL1350
	FCC Class B

MECHANICAL

Case Dimension	85.5 x 69 x 55 mm.
Wirelead	AWG22, 6'
Weight	1.4lbs.
Cooling	Convection cooled
Warranty	24 Months

ELECTRICAL

Topology	Semi-Switching DC Power
Efficiency	60%
Float Charge Voltage	13.8VDC
Output Charge Current	1.0 Amps constant
Ripple & Noise	150 mV
Thermal fuse	115 C
Short Circuit Protection	Yes
Over Current Protection	Yes
Reverse Polarity Protection	Yes

ENVIRONMENTAL

Operating Temp. Range	-5° to 50°C
Storage Temperature	-30°C to +85°C
Relative Humidity	10% to 90%
Altitude	0-3000m

Output Connector

GHC-121000-1P	5.5x2.5mm
GHC-121000-1A	Alligator clips (shielded)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CSB:

[GHC121000P](#)