





Heyco® Liquid Tight Hole Plugs

- V0 Flammability rating.
- Oil tight, rain tight, submersible.
- Multiple trade sizes fit 1/2" to 1" knock-out holes.
- Multiple nominal sizes fit .500" to 1.000" "true size" mounting holes.
- Locks firmly in boxes from .030" (0,8 mm) to .125" (3,2 mm) thick.
- Installs with fingertip pressure (no tool required).
- Trade sizes are  listed under Underwriters' Laboratories File E28430 and CSA Certified by Canadian Standard Association File LR081067C
- True sizes are  recognized under Underwriters' Laboratories File E51579 and CSA Certified by Canadian Standard Association File LR008919C

PANEL DIMENSIONS				PART NO.	DESCRIPTION or Trade Size	PART DIMENSIONS					
Mounting Hole Diameter		Maximum Thickness				Black	A Head Diameter		B Overall Height		C Head Thickness
in.	mm.	in.	mm.				in.	mm.	in.	mm.	in.
.500	12,7	.125	3,2	3830	KOS-LT .500	.920	23,4	.450	11,4	.290	7,4
.625	15,9	.125	3,2	3834	KOS-LT .625	1.030	26,2	.470	11,9	.310	7,9
.750	19,1	.125	3,2	3831	KOS-LT .750	1.150	29,2	.510	13,0	.350	8,9
.875	22,2	.125	3,2	3833	KOS-LT 1/2	1.281	32,5	.500	12,7	.359	9,1
1.000	25,4	.125	3,2	3832	KOS-LT 1.000	1.410	35,8	.560	14,2	.400	10,2
1.093	27,8	.125	3,2	3835	KOS-LT 3/4	1.531	38,9	.546	13,9	.390	9,9
1.375	34,9	.125	3,2	3837	KOS-LT 1	1.796	45,6	.562	14,3	.421	10,7

Standard color black.



Quick
Specs

Material
Flammability Rating

Santoprene™
94V-0


Heyco Metal Liquid Tight Cordgrips NPT Hubs

Steel, for Flexible Cords



CABLE DIA. RANGE				PART NO.	DESC.	Gland Color	NPT HUB SIZE	PART DIMENSIONS							
Min. Dia.	Max. Dia.							A Clearance Hole	B Sealing Nut HEX	C Body Nut O.D.	D Overall Length*	E Exposed Length*			
in.	mm.	in.	mm.					in.	mm.	in.	mm.	in.	mm.	in.	mm.
.150	3,8	.250	6,3	9760	CG 50A-250	Red									
.250	6,3	.350	8,9	9761	CG 50A-350	White									
.350	8,9	.450	11,4	9762	CG 50A-450	Blue	1/2	.875	22,2	1.031	26,2	.937	23,8	1.312	33,3
.450	11,4	.560	14,2	9763	CG 50A-560	Green									
.550	14,0	.650	16,5	9764	CG 50A-650	Brown									
.150	3,8	.250	6,3	9766	CG 75A-250	Red									
.250	6,3	.35	8,9	9767	CG 75A-350	White									
.350	8,9	.450	11,4	9769	CG 75A-450	Blue	3/4	1.109	28,2	1.031	26,2	1.172	29,8	1.312	33,3
.450	11,4	.560	14,2	9770	CG 75A-560	Green									
.550	14,0	.650	16,5	9771	CG 75A-650	Brown									
.650	16,5	.750	19,0	9772	CG 75B-750	Yellow	3/4	1.109	28,2	1.250	31,7	1.187	31,2	1.562	39,7
.750	19,0	.850	21,6	9773	CG 75B-850	Purple									


*May vary slightly depending on cable diameter.



Zinc-Die Cast, for Flexible Cords

Cable Dia. Range				Part No.	Description	NPT Hub Size	Part Dimensions									
Min. Dia.		Max. Dia.					A Clearance Hole		B Sealing Nut HEX		C Body Nut O.D.		D Overall Length*		E Exposed Length*	
in.	mm.	in.	mm.				in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
.190	4,8	.250	6,3	9776	CG 11	1/2										
.260	6,6	.375	9,5	9777	CG 12		.875	22,2	.970	24,6	.900	22,8	1.20	30,5	.80	20,3
.375	9,5	.450	11,4	9778	CG 13											
.440	11,2	.560	14,2	9779	CG 21	3/4										
.500	12,7	.650	16,5	9780	CG 22		1.109	28,2	1.20	30,5	1.10	27,9	1.27	32,3	.87	22,1
.625	15,9	.725	18,4	9781	CG 23											

*May vary slightly depending on cable diameter.



- Multiple sizes with 1/2" to 3/4" NPT hubs, cover a cable diameter range of .150" (3,8 mm) to .850" (21,6 mm).
- Compact design allows fittings to be consecutively ganged—no skipping knockouts—and occupy less “real estate.”
- Color coded label system identifies the cordgrips by wire range/grommet opening.
- Neoprene rubber grommet ensures a permanent rain-tight seal around the cable.
- Galvanized steel pressure ring prevents distortion of the grommet when the sealing nut is tightened.
- Body and sealing nut are made of corrosion resistant machined steel. Zinc plated with special brighteners for an attractive finish.
- Temperature Rating: 221°F (105°C).



- We recommend using the smallest maximum diameter range cordgrip that will fit your application.
- Cast from zinc alloy, Zamac #3.
- Temperature Rating: 140°F (60°C).



Heyco® Pre-Assembly Equipment

For Our Standard Square and RDD Lockit™ Strain Reliefs

Eliminate carpal tunnel syndrome!



Part Number	Description	Use w/ Lockit Part Numbers
0026 ST16 ST13 ST14	RDD 100 Hand Pliers Headlock RDD 100 Autolock RDD 100 Footlock RDD 100	1852, 1870, 1872, 1874
0027 ST17 ST18 ST19	RDD 200, 300 & 400 Series Hand Pliers Headlock RDD 201, 301, 401 Autolock RDD 201, 301, 401 Footlock RDD 201, 301, 401	1855, 1857, 1859, 1861, 1865, 1876, 1878
ST20 ST26 ST27	Headlock RDD 501 Autolock RDD 501 Footlock RDD 501	1868
ST31 ST34	Headlock RDD 601 Footlock RDD 601	1802
ST32 ST33	Headlock RDD 6N-2 Footlock RDD 6N-2	1800
0020 OST1 OST3 OST4	R 100 PLIERS Headlock 100 Autolock 100 Footlock 100	1829, 1832
0025 ST15 OST0 OST6	R 100A/AT PLIERS Headlock 100 A/AT Footlock 100 A/AT Autolock 100 A/AT	1839
0023 ST12 ST10 ST11	R 100W PLIERS Headlock 100 L/W Autolock 100 L/W Footlock 100 L/W	1845, 1847
OST7 OST8 OST9	Headlock 200 Autolock 200 Footlock 200	1834, 1836, 1848

A Headlock™ Standard Square and RDD Lockit

Assembly head for Standard Square and RDD Lockit Strain Reliefs. Simply place a Lockit Strain Relief into the "U" opening of the assembly head. Then place the cable into the bushing body and close the head to secure Strain Relief permanently onto the wire. This completed sub-assembly can then be installed with fingertip pressure into the application's mounting hole—at a later time, in a different place, for lower installed cost!

B Autolock™ Semi-Automatic

Assembly machine for Standard Square and RDD Lockit Strain Reliefs. Suitable for high volume production runs, where batched sub-assemblies are desirable. Includes vibratory feeder bowl, track and head. The operator simply inserts the cable into the assembly head slot, then presses the foot pedal to secure Strain Relief permanently onto the wire. These completed sub-assemblies can be installed with fingertip pressure into the application's mounting hole—at a later time, in a different place, for lower installed cost!

C FootLock™

Assembly machine for Standard Square and RDD Lockit Strain Reliefs. This foot-pedal activated assembly machine is identical to Part Autolock™, except that the gravity fed track is loaded by hand instead of by a vibratory bowl.

**ALL NEW
PRODUCTS!**




Heyco® Louvered Plugs

PANEL DIMENSIONS				PART NO.		DESCRIPTION	PART DIMENSIONS			
Maximum Thickness		Mounting Hole Diameter		Black	White		A Head Diameter		B Overall Height	
in.	mm.	in.	mm.				in.	mm.	in.	mm.
.125	3,2	.875	22,2	2557	2558	LP 875	1.015	25,8	.531	13,5
.125	3,2	1.000	25,4	2559	2560	LP 1000	1.205	30,6	.531	13,5
.125	3,2	1.093	27,8	2561	2562	LP1093	1.218	30,9	.531	13,5
.125	3,2	1.125	28,6							
.125	3,2	1.375	34,9	2567	2568	LP 1375	1.500	38,1	.543	13,8
.125	3,2	1.500	38,1	2569	2570	LP 1500	1.676	42,6	.543	13,8
.125	3,2	2.000	50,8	2594	2595	LP 2000	2.170	55,1	.543	13,8
.250	6,4	2.500	63,5	2596	2597	LP 2.5	2.718	69,0	.823	20,9

Standard color black. Consult Heyco for other colors.

Locking fingers in fractional increments up to the maximum panel thickness.

- Louvers permit the passage of air for ventilation but limits liquid infiltration.
- Locks firmly into panel up to .250" (6,4 mm) thick.
- Quick and easy installation.
- Suitable for ventilation in electronic enclosures, motor housings and metal or plastic panels.
- Withstands a push back force of 35 lbs.



Material	6/6 Nylon
Certifications	UL Pending
Flammability Rating	94V-2
Material Temperature Index	257°F (125°C)—Maximum temperature on part not to exceed 221°F (105°C)

*Quick
Specs*





Heyco® Liquid Tight Hole Plugs

- V0 Flammability rating.
- Oil tight, rain tight, submersible.
- Three trade sizes fit 1/2" to 1" knock-out holes.
- Multiple nominal sizes fit .500" to 1.00" "true size" mounting holes.
- Locks firmly in boxes from .030" (0,8 mm) to .125" (3,2 mm) thick.
- Installs with fingertip pressure (no tool required).
- Trade sizes are  listed under Underwriters' Laboratories File E28430 and certified by Canadian Standard Association File LR081067C.
- True sizes are  recognized under Underwriters' Laboratories File E51579 and  certified by Canadian Standard Association File LR008919C.

PANEL DIMENSIONS				PART NO.	DESCRIPTION	PART DIMENSIONS						
Maximum Thickness		Mounting Hole Diameter				Black	A Head Diameter		B Overall Height		C Head Thickness	
in.	mm.	in.	mm.				in.	mm.	in.	mm.	in.	mm.
.125	3,2	.500	12,7	3830	KOS-LT 500	.920	23,4	.450	11,4	.290	7,4	
.125	3,2	.625	15,9	3834	KOS-LT 625	1.030	26,2	.470	11,9	.310	7,9	
.125	3,2	.750	19,1	3831	KOS-LT 750	1.150	29,2	.510	13,0	.350	8,9	
.125	3,2	.875	22,2	3833	KOS-LT 1/2	1.281	32,5	.500	12,7	.359	9,1	
.125	3,2	1.000	25,4	3832	KOS-LT 1000	1.410	35,8	.560	14,2	.400	10,2	
.125	3,2	1.093	27,8	3835	KOS-LT 3/4	1.531	38,9	.546	13,9	.390	9,9	
.125	3,2	1.375	34,9	3837	KOS-LT 1	1.796	45,6	.562	14,3	.421	10,7	

Standard color black.



Quick
Specs

Material
Flammability Rating

Santoprene™
94V-0


**ALL NEW
PRODUCTS!**


Heyco® Push Lock Cable Clamps

EFFECTIVE CLAMP RANGE				PART NO.		DESCRIPTION	PART DIMENSIONS	
Mounting Hole Diameter		Maximum Panel Thickness		Black	Natural		A	
in.	mm.	in.	mm.				in.	mm.
.187	4,7	.125	3,2	3730	3731	PLCC 1125	1.125	28,6
.187	4,7	.125	3,2	3734	3735	PLCC 1187	1.187	30,1
.187	4,7	.125	3,2	3738	3739	PLCC 1250	1.250	31,1
.187	4,7	.125	3,2	3742	3743	PLCC 1375	1.375	34,9
.187	4,7	.125	3,2	3746	3747	PLCC 1500	1.500	38,1

Standard colors black and natural.

- Quick and easy installation.
- For clamping cable or tubing securely in place.
- Resists corrosion, salt water, weak acids, grease, and common solvents. This feature is not assessed by UL certification or testing.
- Push in arrows for easy installation with no additional hardware.



**ALL NEW
PRODUCTS!**


Heyco® Snap Lock Cable Clamps

EFFECTIVE CLAMP RANGE			PART NO.		DESCRIPTION	PART DIMENSIONS	
Mounting Hole Diameter		SCREW SIZE	Black	Natural		A	
in.	mm.					in.	mm.
.190	4,8	#10	3728	3729	SLCC 1125	1.125	28,6
.190	4,8	#10	3732	3733	SLCC 1187	1.187	30,1
.190	4,8	#10	3736	3737	SLCC 1250	1.250	31,1
.190	4,8	#10	3740	3741	SLCC 1375	1.375	34,9
.190	4,8	#10	3744	3745	SLCC 1500	1.500	38,1

Standard colors black and natural.

- Quick and easy installation.
- For clamping cable or tubing securely in place.
- Locking feature allows for preassembly on wire for ease of installation.
- Resists corrosion, salt water, weak acids, grease, and common solvents. This feature is not assessed by UL certification or testing.
- Locks securely but can be removed and reused.



Material	6/6 Nylon
Flammability Rating	94V-2
Material Temperature Index	257°F (125°C)—Maximum temperature on part not to exceed 221°F (105°C)

Quick Specs