



TLS 2200®/TLS PC Link™ Labels

TLS 2200®/TLS PC Link™ Label Index By Size (Continued)

Diagram	Catalog Number	Labels Per Roll	Material	Color	B-Number	Label Width Inch (mm) A	Label Height Inch (mm) B	Write-On Height Inch (mm) C	Wire Gauge
1.000" (Continued)									
Fig. 7	PTL-31-427-OR	250	Vinyl	Orange	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-31-427-PL	250	Vinyl	Purple	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-31-427-RD	250	Vinyl	Red	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-31-427-YL	250	Vinyl	Yellow	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-31-642	250	Vinyl	White	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	10 to 4
Fig. 7	PTL-31-427	250	Vinyl	White	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	—
Fig. 7	BPTL-31-427	2500	Vinyl	White	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	—
Fig. 7	PTL-31-427-BL	250	Vinyl	Blue	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	—
Fig. 7	PTL-31-427-BR	250	Vinyl	Brown	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	—
Fig. 7	PTL-31-427-GR	250	Vinyl	Green	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	—
Fig. 7	PTL-31-427-GY	250	Vinyl	Gray	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	—
Fig. 7	PTL-31-427-OR	250	Vinyl	Orange	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	—
Fig. 7	PTL-31-427-PL	250	Vinyl	Purple	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	—
Fig. 7	PTL-31-427-RD	250	Vinyl	Red	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	—
Fig. 7	PTL-31-427-YL	250	Vinyl	Yellow	B-427	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	—
Fig. 6	PTL-87-499	250	Nylon	White	B-499	1.000 (25.4)	1.750 (44.5)	—	—
Fig. 6	PTL-21-499	100	Nylon	White	B-499	1.000 (25.4)	2.500 (63.5)	—	Cables
Fig. 6	PTL-21-498	100	Vinyl	White	B-498	1.000 (25.4)	2.500 (63.5)	—	Cables
Fig. 7	PTL-21-427	100	Vinyl	White	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	Cables
Fig. 7	BPTL-21-427	1000	Vinyl	White	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	Cables
Fig. 7	PTL-21-427-BL	100	Vinyl	Blue	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	Cables
Fig. 7	PTL-21-427-BR	100	Vinyl	Brown	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	Cables
Fig. 7	PTL-21-427-GY	100	Vinyl	Gray	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	Cables
Fig. 7	PTL-21-427-OR	100	Vinyl	Orange	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	Cables
Fig. 7	PTL-21-427-PL	100	Vinyl	Purple	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	Cables
Fig. 7	PTL-21-427-RD	100	Vinyl	Red	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	Cables
Fig. 7	PTL-21-427-YL	100	Vinyl	Yellow	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	Cables
Fig. 7	PTL-21-642	100	Vinyl	White	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	Cables
Fig. 7	PTL-21-427-GR	100	Vinyl	Green	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	Cables
Fig. 7	PTL-21-427	100	Vinyl	White	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	—
Fig. 7	BPTL-21-427	1000	Vinyl	White	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	—
Fig. 7	PTL-21-427-BL	100	Vinyl	Blue	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	—
Fig. 7	PTL-21-427-BR	100	Vinyl	Brown	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	—
Fig. 7	PTL-21-427-GR	100	Vinyl	Green	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	—
Fig. 7	PTL-21-427-GY	100	Vinyl	Gray	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	—
Fig. 7	PTL-21-427-OR	100	Vinyl	Orange	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	—
Fig. 7	PTL-21-427-PL	100	Vinyl	Purple	B-427	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	—

Figure 6




Figure 7

