

**TYPE
A**

710 C A 004 M 16 16

Product Series ————

Connector Designator (C, D, E, J, or K) (Pages F-4 to F-6) ————

Angle: ————

A = 90°

B = 45°


S = Straight

Dash No. (Table II) ————


Shell Size (Table I) ————

Finish (Table III) ————


Basic No. ————




STYLE 2



STRAIGHT



90°



45°

Metric dimensions (mm) are indicated in parentheses.
Tubing shown for reference only.

710-004

**Non-Environmental User-Installable Straight, 45° & 90°
Connector Fittings for Series 72 Annular Convulated Tubing**



Series 72
Convulated
Tubing

TABLE I

SHELL SIZE C,D,E,J or K	E DIMENSION MAX		
	C CONN	D,E,J, CONN	K CONN
08	—	1.000 (25.4)	1.000 (25.4)
10/11	—	1.000 (25.4)	1.000 (25.4)
12/13	1.735 (44.1)	1.000 (25.4)	1.000 (25.4)
14/15	1.915 (48.6)	1.000 (25.4)	1.000 (25.4)
16/17	1.915 (48.6)	1.000 (25.4)	1.166 (29.6)
18	1.915 (48.6)	1.000 (25.4)	1.166 (29.6)
20	1.915 (48.6)	1.000 (25.4)	1.166 (29.6)
22	1.915 (48.6)	1.000 (25.4)	1.166 (29.6)
24	1.915 (48.6)	1.000 (25.4)	1.166 (29.6)
28	1.915 (48.6)	—	1.166 (29.6)
32	1.915 (48.6)	—	1.166 (29.6)
36	1.915 (48.6)	—	1.166 (29.6)
40	1.915 (48.6)	—	1.437 (36.5)

TABLE II

DASH NO.	F MAX	G MAX	H MAX	J MAX	K MAX	L DIA
09	1.196 (30.4)	1.780 (45.2)	1.126 (28.6)	1.795 (45.6)	.281 (7.1)	.875 (22.2)
12	1.196 (30.4)	1.780 (45.2)	1.126 (28.6)	1.795 (45.6)	.370 (9.4)	1.000 (25.4)
16	1.415 (35.9)	1.895 (48.1)	1.273 (32.3)	1.905 (48.4)	.500 (12.7)	1.125 (28.6)
20	1.587 (40.3)	2.065 (52.5)	1.533 (38.9)	2.095 (53.2)	.625 (15.9)	1.250 (31.8)
24	1.587 (40.3)	2.065 (52.5)	1.533 (38.9)	2.095 (53.2)	.750 (19.1)	1.438 (36.5)
28	1.913 (48.6)	2.175 (55.2)	1.718 (43.6)	2.245 (57.0)	.875 (22.2)	1.625 (41.3)
32	1.913 (48.6)	2.175 (55.2)	1.718 (43.6)	2.245 (57.0)	1.000 (25.4)	1.750 (44.5)
40	1.997 (50.7)	2.345 (59.6)	1.915 (48.6)	2.295 (58.3)	1.250 (31.8)	2.000 (50.8)

TABLE III

SYMBOL FINISH	
B	Olive Drab over Cadmium Plate
J	Gold Iridite over Cadmium Plate over Nickel
M	Electroless Nickel
N	Olive Drab over Cadmium Plate over Nickel
NC	Zinc-Cobalt, Olive Drab
NF	Olive Drab over Cadmium Plate over Electroless Nickel (500 Hour Salt Spray)
T	Bright Dip Cadmium Plate over Nickel

Metric dimensions (mm) are indicated in parentheses.

When tubing I.D. max exceeds inside
diameter of connector shell, style 2 will be
supplied. Refer to pages F-15 and F-16.