

8791
Open end fitting
16 Z

- For accessing bolts in cramped and hard-to-access locations - easy to change
- Forged
- Chrome-vanadium steel, chrome-plated
- With eject-pin for unlocking



Code	No.	Ø	 mm	mm 	 mm	Depth gauge	
7774470	8791-07	16	7	5	20.5	32	80
7774550	8791-08	16	8	5	20.5	32	80
7774630	8791-09	16	9	5	20.5	32	80
7710070	8791-10	16	10	7	29.0	32	90
7710150	8791-11	16	11	7	29.0	32	90
7676890	8791-12	16	12	7	29.0	32	90
7710230	8791-13	16	13	8	34.5	32	120
7710310	8791-14	16	14	8	34.5	32	120

Code	No.	Ø	 mm	mm 	 mm	Depth gauge	
7710580	8791-15	16	15	8	34.5	32	120
7710660	8791-16	16	16	9	41.5	32	160
7710740	8791-17	16	17	9	41.5	32	160
7676970	8791-18	16	18	9	41.5	32	160
7710820	8791-19	16	19	10	45.0	32	180
7710900	8791-20	16	20	10	45.0	32	180
7677000	8791-21	16	21	10	45.0	32	180
7711040	8791-22	16	22	11	56.0	32	220
7711120	8791-24	16	24	11	56.0	32	220
7711200	8791-27	16	27	12	60.5	32	260
7774710	8791-30	16	30	12	68.0	32	300
7774980	8791-32	16	32	12	68.0	32	300
1552317	8791-36	16	36	12	68.0	32	300

Code	No.	Ø	 AF	mm 	 mm	Depth gauge	
1211421	8791-1/4AF	16	1/4	5	20.5	32	90
7720030	8791-5/16AF	16	5/16	5	20.5	32	80
1211447	8791-3/8AF	16	3/8	7	29.0	32	90
7720110	8791-7/16AF	16	7/16	7	29.0	32	90
7720380	8791-1/2AF	16	1/2	8	34.5	32	90
7720460	8791-9/16AF	16	9/16	8	34.5	32	120
7720540	8791-5/8AF	16	5/8	9	41.5	32	160
7720620	8791-11/16AF	16	11/16	9	41.5	32	160
7720700	8791-3/4AF	16	3/4	10	45.0	32	180
1211439	8791-13/16AF	16	13/16	10	45.0	32	90

Code	No.	Ø	 AF	mm 	 mm	Depth gauge	
7720890	8791-7/8AF	16	7/8	10	45.0	32	220
7720970	8791-15/16AF	16	15/16	11	56.0	32	220
7721000	8791-1AF	16	1	11	56.0	32	220
7721190	8791-1.1/16AF	16	1.1/16	12	60.5	32	260
7721270	8791-1.1/8AF	16	1.1/8	12	68.0	32	300
7776170	8791-1.3/16AF	16	1.3/16	12	68.0	32	300
7776250	8791-1.1/4AF	16	1.1/4	12	68.0	32	300
7776330	8791-1.5/16AF	16	1.5/16	12	68.0	32	300