

## VGA Coax Monitor Easy Pull Extension Cable, High Resolution cable with RGB coax (HD15 M/F) 100-ft.

MODEL NUMBER: **P501-100**



### Description

Tripp Lite's 100 ft. SVGA/VGA Easy Pull Monitor Extension Cable w/ Connectors makes running long length video cables a snap. The pull-apart design allows the cable to be run through conduit or other tight areas that a HD15 connector wouldn't fit through. Diameter of the circular DIN end is only 7/8". Circular Easy Pull connector is threaded to ensure maximum security once the cable is reattached. The mini-coax (RGB) and paired video wire construction delivers superior signal quality. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both the high density DB15 male and high density DB15 female connectors are molded and have integral strain relief to ensure they last a long time.

### Features

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- RGB 75-ohm coax construction for maximum video resolution
- HD15 male to HD15 female molded connectors
- Supports resolutions up to 1600 x 1200

## Specifications

OVERVIEW	
Intended Application	Connecting Peripherals
Cable Type	MONITOR
Display Style	Easy Pull
INPUT	

### Highlights

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- 75ohm mini-coax (RGB) and paired video wire construction delivers outstanding signal quality
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection

### Applications



- Suspended ceilings, walls, conduit or anywhere too small to fit a standard HD15 cable during installation.

### Package Includes

- 100 ft. Male/Female Easy Pull SVGA/VGA Monitor Extension Cable w/ Connectors
- Wallplate with HD15 cutout



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Cable Length (ft.)	100
Cable Length (m)	30.48
<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332142269
<b>PHYSICAL</b>	
Color	Black
Style	Video Cables
<b>CONNECTIONS</b>	
Connector A	 HD15 (MALE)
Connector B	 HD15 (FEMALE)
<b>CERTIFICATIONS</b>	
Certifications	RoHS-Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

## Related Items

### Optional Products

Model Number	Description	Qty.
<a href="#">B114-002-R</a>	VGA/SVGA 350MHz Video Splitter - 2 Port (HD15 M/2xF)	1
<a href="#">B114-004-R</a>	VGA/SVGA 350MHz Video Splitter - 4 Port (HD15 M/4xF)	1
<a href="#">P120-000</a>	DVI Male to VGA Female Adapter (Analog DVI-M to HD15F)	1
<a href="#">P158-000</a>	Compact Gold HD15 Gender Changer (HD15M/M)	1
<a href="#">P160-000</a>	Compact Gold HD15 Gender Changer (HD15F/F)	1
<a href="#">P501-050</a>	50-ft. SVGA/VGA Easy-Pull Gold Monitor Extension Cable with RGB Coax, (HD15 M/F)	1
<a href="#">P503-050</a>	50-ft. Easy Pull All-in-One SVGA/VGA Monitor Cable with Connectors, (HD15 M/M)	1



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

P503-100	100-ft. Easy Pull All-in-One SVGA/VGA Monitor Cable with RGB Coax, (HD15 M/M)	1
----------	---	---

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:  
<http://www.tripplite.com/sku/P501-100>.

---

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.