




6 A 2P plugs and extensions and TV plugs




Ø4 mm pin
For 2-wire cables (max. Ø9 mm)
For class II appliances



Pack	Cat.Nos	2P - plastic - 6 A
20	501 27	○ Plug - white
10	501 28	○ Extension - white
20	501 29	● Plug - old gold
10	501 30	● Extension - old gold

Pack	Cat.Nos	2P - rubber - 6 A
20	501 67	● Plug - black
10	501 68	● Extension - black

Pack	Cat.Nos	TV plugs
50	500 09	Ø9.52 mm Male plug
50	500 10	Female plug



16 A 2P+⊕ plugs and extensions French standard



Pack	Cat.Nos	2P+⊕ - plastic - 16 A
		Automatic cable grip Plastic plug and extension For round cable max. Ø11 mm Ø4.8 mm pin for class I appliances Extension equipped with child protection shutters
		○ Straight outlet plug - white
		○ Side outlet plug - white
		○ Extension - white
20	502 15	○ Straight outlet plug - grey
20	502 16	○ Side outlet plug - grey
10	502 17	○ Extension - grey
20	502 34	● Straight outlet plug - black
20	502 38	○ Straight outlet plug with extraction handle - Annela - white
10	502 21	○ Extension - Annela - white
		Screw type cable grip Plastic plug and extension For round cable max. Ø11 mm Ø4.8 mm pin for class I appliances Extension equipped with child protection shutters with extraction handle
20	502 30	● Plug - grey
10	502 31	● Extension - grey

Pack	Cat.Nos	2P+⊕ - rubber - 16 A
		Screw type cable grip Rubber plug and extension 250 V~ For class I appliances
10	502 45	Straight outlet plug - black For round cable max. Ø11 mm
10	502 46	Extension - black For round cable max. Ø11 mm
10	502 52	Side outlet plug with extraction handle - black French, German standard (NF-USE, VDE, CEBEC, ICEMA and OVE) For round cable max. Ø12.5 mm