




Two-Piece - Inner sleeve

T&B Catalog Number:

GSB071

UPC Number:

78621081279

Status:

Active

Description:

Two Piece Inner Sleeve Connector for Hexagonal Range, Length 7.9mm, Inner Diameter 1.87mm, Outer Diameter 2.44mm, Color Green, Hard Bronze, Tin Plated

Features

Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Inner sleeve for the Hexagonal Range (the corresponding outer sleeve is crimped with a hand tool and the result is a hexagonal-shaped crimp), for grounding shielded and coaxial cables. The sleeves are color coded according to their size. Millions of installations in communications, aerospace, electronic, telephone, radio and TV applications.

General

Material	Hard bronze
Finish	Tin plated (per MIL-T-10727A)
Color	Green

Dimension Information

Length (inches)	.311
Length (mm)	7.9
Inner Diameter (inches)	.071
Inner Diameter (mm)	1.87
Outer Diameter (inches)	.096
Outer Diameter (mm)	2.44

Specifications

MIL Specification	21981-071
-------------------	-----------

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000206
Overview	Available on Website
Installation Overview	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321

