





REV.	DATE	DESCRIPTION
NC	05/31/07	INITIAL RELEASE



RECOMMENDED
MOUNTING HOLE



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex			
7						DRAWN G.R.S.	05/31/07				
6	HEX NUT	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	CHECKED		PART DESCRIPTION BNC TWIN BULKHEAD RECEPT. JACK			
5	LOCK WASHER	BRASS	NICKEL	1		ISSUED					
4	CONTACT PIN	PHOS. BRONZE	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	SHEET 1 OF 1		PART NO. 162109			
3	CONTACT PIN	BRASS	GOLD	1							
2	INSULATOR	PBT	WHITE	2	DO NOT SCALE DRAWING	CAD FILE	C:/162/162109.DWG	DWG. NO. 162109.DWG REV. NC SIZE A SCALE NA			
1	BODY	BRASS	NICKEL	1							
	DESCRIPTION	MATERIAL	FINISH	QTY							