



Open Racks
Heavy Duty Steel Rack



Design Features

These heavy duty racks, an extension of the Bud RR-1265 Series, are available in 6' and 7' heights for 19" wide panel spaces. Panel mounting holes are #12-24 tapped on E.I.A. universal spacing. (Use #9260 screws - order separately) Panel mounting holes are located on front flanges only.

Base Angles .25" x 3.50" x 4.87"

Top Angles .12" x 2.09" x 1.56"

Uprights: .18" x 3.00" x 1.28"

Overall Width 20.37" for 19" rack,

Overall Depth 12.75 base, 3.00" upright, 6.12" top

Features

Racks are shipped knocked down in two (2) cartons, with all necessary assembly hardware included.

Finishes

Finish: Black Texture (BT)

Heavy Duty Steel Rack				
Catalog Number	Drawings	Panel Space	Height	Weight Lbs.
RR-1265		66.50" x 19.00"	72.25"	64
RR-1269		77.00" x 19.00"	82.75"	73




PART
NAME

OPEN RELAY RACK

PART
No.

RR-1265 TO RR-1292

MATERIAL:


TOP BARS _____ 12 GA. STEEL
 BASE ANGLES _____ 1/4" THK. STEEL
 UPRIGHTS _____ 3/16" THK. STEEL

FINISH:


BLACK TEXTURED

UPRIGHTS ARE TAPPED #12-24 ON
 E.I.A. UNIVERSAL SPACING.



UNIT SHIPPED KNOCKED DOWN.



FRONT

NOTE:

ALTERNATE METHOD
 OF MOUNTING TOP
 BARS



REAR

PART NO.	PANEL SPACE A	B	C	D	E	F
RR-1265	66.500	72.156	17.937	18.312	20.375	16.000
RR-1269	77.000	82.656	17.937	18.312	20.375	16.000
RR-1270	101.500	107.156	17.937	18.312	20.375	16.000
RR-1290	66.500	72.156	21.937	22.312	24.375	20.000
RR-1291	77.000	82.656	21.937	22.312	24.375	20.000
RR-1292	101.500	107.156	21.937	22.312	24.375	20.000