






LDC	DIST	REVISIONS				DATE	DWN	APP'D
		P	LTR	DESCRIPTION				
		A		FIRST VERSION				



NOTES :

- △ MATERIALS AND FINISH:
- HOUSING: PA66
- CONTACTS: COPPER, FINISH: TIN OVER NICKEL UNDERPLATE
2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
3. WIRE TYPES AND SIZES ACCEPTED
WIRE RANGE: 14AWG~20AWG.
STRIP LENGTH: 9.0mm~10.0mm
4. PACKAGED IN TRAY.
5. CURRENT RATING: 10Amp AC300V.
6. OPERATION TEMPERATURE: -40°C TO +105°C
7. THIS PART NO. IS THE SAME STRUCTURE AS THE SERIES: 2834097
THE DATASHEET AND MORE DETAILS PLEASE FOLLOW THE SERIES: 2834097

COLOR	DIM A	NO. OF POSITIONS	PART NO	④	③	②	①
				WIRE PROTECTOR	CONTACT	COVER	HOUSING
GRAY	40.90	8 POSN	2834097-7				
	35.90	7 POSN	2834097-6				
	30.90	6 POSN	2834097-5				
	25.90	5 POSN	2834097-4				
	20.90	4 POSN	2834097-3				
	15.90	3 POSN	2834097-2				
	10.90	2 POSN	2834097-1				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DESIGNER	INTEGRITY	DATE	02DEC2015	REV	02DEC2015	NAME	TE Connectivity
CHKD	02DEC2015	DATE	02DEC2015	REV	02DEC2015	NAME	TE Connectivity
APP'D	02DEC2015	DATE	02DEC2015	REV	02DEC2015	NAME	TE Connectivity
008-137147	008-137147	008-137147	008-137147	008-137147	008-137147	008-137147	008-137147
114-137147	114-137147	114-137147	114-137147	114-137147	114-137147	114-137147	114-137147
114-137147	114-137147	114-137147	114-137147	114-137147	114-137147	114-137147	114-137147

5.0 Horizontal Entry Screwless Connector

SIZE CODE 00779 C-2834097

RESTRICTED TO

SCALE 1:1

SHEET 1 OF 1

REV A