



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
FT	0				G	REVISE PER ECN 0G3B-0319-00	14JUL00	SU/GS
					H	REV PER EC 0G3B-0351-01	18JAN02	GS
					H	REVISED PER ECO-09-020935	08SEP09	AEG

A	.34	.043	--	12	6.35	.250	UNPL	18	0.15	.006	03142	5-192038-0	OBSOLETE	16
A	.34	.030	--	12	6.35	.250	3-2	18	0.15	.006	03028	4-192038-9		
A	.34	.030	--	12	6.35	.250	1-2	18	0.15	.006	03086	4-192038-8		
A	.34	.030	--	12	6.35	.250	UNPL	18	0.15	.006	03074	4-192038-7	OBSOLETE	16
A	--	--	--	12	6.30	.248	UNPL	19	0.30	.012	--	4-192038-6	15	15
A	--	--	--	12	6.30	.248	UNPL	19	0.28	.011	--	4-192038-5	15	15
A	.35	.034	--	12	6.30	.248	3-2	19	0.25	.010	03025	4-192038-4	16	
A	.35	.034	--	12	6.30	.248	1-2	19	0.25	.010	03147	4-192038-3	OBSOLETE	
A	.35	.034	--	12	6.30	.248	UNPL	19	0.25	.010	03111	4-192038-2		
A	.32	.038	--	12	6.00	.236	4-2	17	0.20	.008	03137	4-192038-1		
A	.32	.038	--	12	6.00	.236	3-2	17	0.20	.008	03023	4-192038-0		
A	.32	.038	--	12	6.00	.236	1-2	17	0.20	.008	03065	3-192038-9	16	
A	.32	.034	--	12	6.00	.236	UNPL	17	0.20	.008	03061	3-192038-8	OBSOLETE	
A	.33	.034	--	12	6.00	.236	3-2	17	0.15	.006	03022	3-192038-7	16	
A	.33	.034	--	12	6.00	.236	1-2	17	0.15	.006	03113	3-192038-6	16	
A	.33	.034	--	12	6.00	.236	UNPL	17	0.15	.006	03021	3-192038-5	OBSOLETE	
NOT AVAILABLE												3-192038-4	15	
A	.35	.020	--	13	6.00	.236	--	17	0.12	.005	03085	3-192038-3	16	
												3-192038-2	16	
A	.26	.034	--	12	5.00	.197	3-2	15	0.20	.008	03019	3-192038-1	OBSOLETE	
A	.26	.034	--	12	5.00	.197	1-2	15	0.20	.008	03131	3-192038-0		
A	.26	.034	--	12	5.00	.197	UNPL	15	0.20	.008	03130	2-192038-9		
A	.26	.031	--	12	5.00	.197	3-2	15	0.15	.006	03018	2-192038-8		
A	.26	.031	--	12	5.00	.197	1-2	15	0.15	.006	03064	2-192038-7	16	
A	.26	.031	--	12	5.00	.197	5	15	0.15	.006	03103	2-192038-6	OBSOLETE	
A	.26	.031	--	12	5.00	.197	UNPL	15	0.15	.006	03060	2-192038-5	OBSOLETE	
A	.23	.034	--	12	4.00	.157	3-2	14	0.20	.008	03013	2-192038-4	16	
A	.23	.030	--	12	4.00	.157	3-2	14	0.15	.006	03012	2-192038-3	16	
A	.21	.030	--	12	3.50	.138	3-2	13	0.15	.006	03011	2-192038-2	16	
A	.21	.034	--	12	3.17	.125	3-2	12	0.20	.008	03010	2-192038-1	OBSOLETE	
A	.21	.034	--	12	3.17	.125	1-2	12	0.10	.004	03132	2-192038-0		
A	.21	.034	--	12	3.17	.125	5	12	0.10	.004	03133	1-192038-9		
A	.21	.034	--	12	3.17	.125	UNPL	12	0.10	.004	03134	1-192038-8		
A	.20	.030	--	12	3.00	.118	3-2	11	0.15	.006	03009	1-192038-7		
A	.19	.030	--	12	3.00	.118	3-2	10	0.15	.006	03008	1-192038-6		
A	.18	.030	--	12	2.67	.105	3-2	9	0.15	.006	03007	1-192038-5	16	
A	.18	.030	--	12	2.31	.091	3-2	8	0.15	.006	03006	1-192038-4		
A	.15	.030	--	12	2.03	.080	3-2	7	0.15	.006	03005	1-192038-3		
A	.15	.030	--	12	1.70	.067	3-2	6	0.15	.006	03004	1-192038-2		
C	--	.038	NOTE 14	12	--	--	3-2	--	0.20	.008	03000	1-192038-1	OBSOLETE	
C	--	.038	NOTE 14	12	--	--	1-2	--	0.20	.008	03095	1-192038-0		
C	--	.038	NOTE 14	12	--	--	UNPL	--	0.20	.008	03077	192038-9		
C	--	.034	NOTE 14	12	--	--	4-2	--	0.15	.006	03123	192038-8		
C	--	.034	NOTE 14	12	--	--	3-2	--	0.15	.006	03053	192038-7	OBSOLETE	
C	--	.034	NOTE 14	12	--	--	1-2	--	0.15	.006	03104	192038-6		
C	--	.034	NOTE 14	12	--	--	UNPL	--	0.15	.006	03001	192038-5	16	
NOT AVAILABLE												192038-4		
NOT AVAILABLE												192038-3	OBSOLETE	
NOT AVAILABLE												192038-2		
NOT AVAILABLE												192038-1		



STYLE A
(FEMALE)

1. FINISH-SILVER PLATE 200 μ IN MIN THICK.
2. FINISH-NICKEL PLATE 40 μ IN MIN THICK.
3. FINISH-GOLD PLATE 10 μ IN MIN THICK.
4. FINISH-GOLD PLATE 50 μ IN MIN THICK.
5. FINISH-NICKEL PLATE 80 μ IN MIN THICK.
6. FINISH-TIN PLATE 300 μ IN MIN THICK.
7. NOT USED.
8. NOT USED.
9. NOT USED.
10. NOT USED.
11. PLATING NOTE ARE TO BE INTERPRETED AS FOLLOWS, 6-8 AS 6 OVER 8.
12. MATERIAL-CDA172, BeCu.
13. MATERIAL-STAINLESS STEEL.
14. PRODUCT IS SOLD BY THE FOOT.
15. OBSOLETE PART NUMBER.
16. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

STYLE	FREE DIA	LH	LENGTH	MAT'L (NOTE)	MATING PIN ϕ REF	PLATING NOTE NO.	NUM LOUV	MAT'L THK	REF	PART NO.
-------	----------	----	--------	--------------	-----------------------	------------------	----------	-----------	-----	----------

											DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 1 PLC DEC $\pm$ 0.5 [.02] 2 PLC DEC $\pm$ 0.25 [.010] ANGLES $\pm$ -	DR RA JAYNE 08-13-91	AMP Incorporated Harrisburg, PA 17105-3608		
											CHK RA JAYNE 08-13-91				
SEE TABLE											MATERIAL	APPD RA JAYNE 08-13-91	CONTACT BAND,FEMALE		
											FINISH	APPD RA JAYNE 08-13-91			
SEE TABLE											SEE TABLE	APPLICATION SPEC	SIZE	CAGE CODE 00779	DRAWING NO 192038
											SEE TABLE	-	SCALE	NTS	SHEET 1 OF 2
											SEE TABLE	WEIGHT -			

