

Mounting brackets Festebraketter


TYPE FBS 205825

Dim./Mål: 135x20x10mm
2 mounting brackets per unit.
Designed for type:
2 festebraketter pr. enhet.
Beregnet for type:
719, 8421, 9522, 9150, 9521,
9221, 9527, 2026, 9623,
2024, 9726, 2023, 2047




TYPE FAS 207724

Dim./Mål: 80x20x8mm
2 mounting brackets per unit.
Designed for type:
2 festebraketter pr. enhet.
Beregnet for type:
9120, 9320, 9322



TYPE LME 207818

Dim./Mål: 93x75mm
1 mounting bracket per unit.
Designed for type:
1 festebrakett pr. enhet.
Beregnet for type:
6820, 8930, 8931, 6823, 8937, 7504



TYPE FCS 202718

Dim./Mål: 110x30x12mm
2 mounting brackets per unit.
Designed for type:
2 festebraketter pr. enhet.
Beregnet for type:
8921, 9260, 2043,
2044, 9660, 2025



TYPE 202906

Dim./Mål: 46x47x36mm
1 mounting bracket per unit.
Designed for type: *
1 festebrakett per enhet.
Beregnet for type: *
2240, 2121, 2122, 2124,
2125, 2115



TYPE 201565

Dim./Mål: 60x69x38mm
1 mounting bracket per unit.
Designed for type: *
1 festebrakett per enhet.
Beregnet for type: *
9920, 9921, 9922, 9940,
2246, 2215, 2515, 2541, 2544



TYPE 201970

Dim./Mål: 72x82x45mm
1 mounting bracket per unit.
Designed for type:
1 festebrakett per enhet.
Beregnet for type:
2020, 2022, 2040, 2415, 2440, 2641



TYPE 9000-16 KLIPS ENGAGEMENT FOOT

FM4 engagement foot for TS-35 (35 mm DIN rail). Used in combination with mounting brackets. Supplied in two-pack.
FM4 klips for TS-35 (35 mm DIN skinne).
Brukes i kombinasjon med festebraketter.
Pakket i poser à 2 stk.



Miscellaneous Diverse



TYPE 131306

2-pin IEC 320 cord set, 1,8 meter
2-pins IEC 320 kabel, 1,8 meter



TYPE 013095

3-pin IEC 320 cord set, 1,8 meter
3-pins IEC 320 kabel, 1,8 meter



TYPE 9998

Remote control with 5 m cable for inverter models 9987, 9988 and 2287
Fjernkontroll med 5 m kabel for inverter modellene 9987, 9988 og 2287

* Not for exch. AC models. / * Ikke for modeller med utskiftbare AC plugger