


Capacitor, film, 1 uF, +/-20% Tol, -55/+105C, Safety: X2, 275VAC, Lead Spacing=22.5 mm, Not for new design.



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	26	MAX
H	23	MAX
T	13.5	MAX
S	22.5	+/-0.4
LL	6	NOM
F	0.8	NOM

General Information	
Supplier:	KEMET
Brand:	Rifa
Miscellaneous Electrical:	Not for new design.

Specifications	
Capacitance:	1 uF
Rated Temperature:	105C
Voltage @ rated temp:	760VDC
Voltage AC:	275VAC
Tolerance:	+/-20%
Body Type:	Radial Box
Dielectric:	Metallized Polypropylene
Application:	Safety: X2
Temperature Range:	-55/+105C
Dissipation Factor @ 1 kHz:	0.1%
Dissipation Factor @ 10 kHz:	0.4%
Insulation Resistance:	10 GOhm
Maximum dVdT:	100 V/us

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Tray
Package Quantity:	200

Agency Approvals	
Approvals:	ENEC,UL,cUL

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.