



Surface Mount Transistors

Darlington Transistors—NPN

Type No.	Case Style	V _{CE0} (V) Min	V _{CE0} (V) Min	V _{BE0} (V) Min	I _{CE0} * (μA) Max	V _{CB} (V)	h _{FE} Min	h _{FE} Max	I _C & V _{CE} (mA) (V)	V _{CE(SAT)} (V) Max	V _{BE(SAT)} (V) Min	I _C (mA) Max	C _{ob} (pF) Max	f _T (MHz) Min	I _C (mA) Max	Process No.
MMBT 6426	TO-236 (49)	40	40	12	0.05	30	20,000	200,000	10 5	1.2		50	7	150	10	05
MMBT A12	TO-236 (49)	20		10	0.1	15	20,000		10 5	1.0		10				05
MMBT A13	TO-236 (49)	30		10	0.1	30	5,000		10 5	1.5		100		125	10	05
MMBT A14	TO-236 (49)	30		10	0.1	30	10,000		10 5	1.5		100		125	10	05

6-25

T-31-01

Surface Mount Devices

6