

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [111025-1206](#)
Status: **Active**
Overview: [CXP Interconnect System](#)
Description: iPass+™ High-Speed Channel (HSC) CXP Cable Assembly, 12X Quad Data Rate (QDR), 84 Circuits, 6.00m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E72548

General

Product Family Cable Assemblies
Series [111025](#)
Assembly Configuration Dual Ended Connectors
Comments Hot Pluggable, Pull to Release Style Latch
Connector to Connector InfiniBand* 12x Both Ends, iPass-to-iPass
Overview [CXP Interconnect System](#)
Product Name InfiniBand*, iPass+™
UPC 883906021443

Physical

Cable Length 6.0m
Circuits (Loaded) 84
Gender Male
Lock to Mating Part Yes
Material - Metal Zinc Alloy
Material - Plating Mating Gold
Net Weight 5288.401/g
Packaging Type Bag
Single Ended No
Wire/Cable Type Twin-ax


Electrical

Current - Maximum per Contact 0.5A
Impedance 100#
Voltage - Maximum 30V AC

Material Info

Reference - Drawing Numbers

Sales Drawing SD-111025-120



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[111025Series](#)

Mates With

[76105-0584](#) iPass™+ 84 Circuit Connector