


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	MATERIAL SUFFIX	A	B	C	D	E	F	USE WITH THESE CABLE TIE CROSS SECTIONS	WEIGHT (g) lbs/100 pcs.
TM1A	NONE	.513 (13.0)	.316 (8.0)	.230 (5.8)	.130 (3.3)	.067 (1.7)	.125 (3.2)	MINIATURE ONLY	.07 (31.8)
TM2A	NONE -39	.630 (16.0)	.425 (10.8)	.275 (7.0)	.215 (5.5) ±.020 ±(.5)	.060 (1.5) ±.020 ±(.5)	.155 (3.9)	MINIATURE INTERMEDIATE STANDARD	.15 (67.9)
TM3A	NONE	.875 (22.2)	.620 (15.8)	.375 (9.5)	.320 (8.1) ±.020 ±(.5)	.088 (2.2) ±.020 ±(.5)	.210 (5.3)	MINIATURE INTERMEDIATE STANDARD LIGHT HEAVY	.36 (163.4)



SECTION A - A

MATERIAL SUFFIX	MATERIAL	COLOR
NONE	NYLON 6/6	NATURAL
-39	HEAT STABILIZED NYLON	NATURAL

NOTE:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. CUSTOMER MUST SUPPLY ADHESIVE FOR FASTENING.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G03597JV_DC_GB0239CM/00B

PANDUIT

CORP. TINLEY PARK, ILLINOIS

TIE MOUNT - TM_A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
00B	10/01/08	ARHA		-39 MATERIAL ADDED: TABLES MODIFIED: CHANGED FILENAME AND REVISION STYLE.	GB0239CM		00B	
7	8-16-02	LGG		CHG TM3A DIM ON 'E' (WAS .089(2.3) ADDED ± TO 'E' & 'D' FOR TM2A & TM3A	GB0239CM	7		
6	07-31-00	GDH		TM3A DIM. 'E' WAS: .080(12.0), ±.020(1.5) 1	GB0239CM	6		
5	7-19-99	CGSM		REMOVED BOLD FONTS FROM DIM TABLE	GB0239CM	5		
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY GDH

DATE 02-20-95

CHK'D KLN

MAT'L: NYLON 6/6
NATURAL

SCALE NONE

DRAWING NO.

GB0239CM

DWG

SIZE A