


IEEE 1394 Firewire, 4 Pin Plug Solder Type

154-AVW10-E, 154-AVW10-34K-E,
154-AVW10-U4K-E, 154-AVW10-D4K-E

KOBICONN

IEEE 1394 Firewire, 4 Pin Plug Solder Type



Dimensions: mm (in.)

Specifications	
Voltage:	30 VAC (R.M.S.)
Current:	1.0 Ampere max./ contact at 30°C T-Rise
Temperature:	80°C
Contact Resistance:	30 Miliohms max. initial
Insulation Resistance:	100 Megaohms min.
Dielectric Withstanding Voltage:	100 VAC at sea level
Contact Plating:	30μ" Au
Shell Plating:	Nickel plating
Clamp & SR Dimensions:	Clamp ø4.0mm, SR ø4.5mm
RoHS Compliant	

Date Last Revised: 7-26-07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301001

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

154-AVW10-E, 154-AVW10-34K-E,
154-AVW10-U4K-E, 154-AVW10-D4K-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-AVW10-E](#)