


# ED3100/X



1-n poles, Spacing 5.0 mm adjustable to 5.08 mm

insert required no. of poles **x**

How to order see page 5



## Ratings:

Rated Voltage

300 V

250 V

Rated Current

16 A

24 A (T60)

Wire Size

AWG 28-14

2.5 mm<sup>2</sup>

Test Voltage

2.0 kV

## Max. Rated Cross Section

Single Wire (solid)

2.5 mm<sup>2</sup>

Stranded Wire (flexible)

2.5 mm<sup>2</sup>

Stranded wire with Ferrules

1.5 mm<sup>2</sup>

## Dimensions

Spacing

5.0 mm (5.08 mm)

PCB Hole Diameter

1.0 mm (2x)

Stripped Length

6.0 mm

## Materials

Insulating Material

PA

Flammability Class

UL94 V-0

Temperature Range

-30°C/+105°C

Cage Clamp


Stainless Steel

Wire Guard

Cu

## Color

Slade Grey



**P = No. of poles**