


CATALOG LISTING
1SE113-3
PAGE 1 OF 1
RELEASE NO. PR-12435
CHECK
REPLACES
FORMTEK
DRAWN
TMM
20 SEP 83
CHECK
GLH
26 SEP 83
CHECK
3




NOTES

- ① MOUNTING HOLES WILL ACCEPT $.087$ MAX DIA PINS OR SCREWS ON $.375 \pm .002$ CENTERS
- ② ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- ③ WEIGHT OF SWITCH ONLY IS $.26$ OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS 1.40 OZ MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE - — — — — 5-17 OZ	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
DIFFERENTIAL FORCE — — — —	250 VAC — — — — — 5 AMP	ONE PLACE (.0) $\pm .030$	
RELEASE FORCE — — — — — 4 OZ MIN	30 VOLTS DC RATING	TWO PLACE (.00) $\pm .015$	
PRETRAVEL — — — — — .004 MIN	INDUCTIVE — — — — — SEA LEVEL 3 AMP	THREE PLACE (.000) $\pm .005$	
DIFFERENTIAL TRAVEL — — — — — .004 MAX	RESISTIVE — — — — — SEA LEVEL 5 AMP	ANGLES $\pm$	
OVERTRAVEL — — — — — .003 MIN	MAXIMUM INRUSH — — — — — 50,000 FT 5 AMP	WEIGHT ③	
FREE POSITION — — — — —	MAXIMUM INRUSH — — — — — 24 AMP		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1SE113-3](#)