

Crimping pliers - CRIMPFOX-SC 1,5-M - 1212725

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for non-insulated slip-on sleeves 2.8 and 4.8 mm, 0.1 - 1.5 mm², B crimp

Why buy this product

- ✓ Crimping pliers for uninsulated slip-on sleeves
- ✓ Consistently high crimping quality
- ✓ Marked die stations for precise processing of corresponding cross sections
- ✓ Unlockable pressure lock



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 857840
GTIN	4046356857840

Technical data

Dimensions

Length (b)	204 mm
Width (a)	22 mm
Height	76 mm

General

Compression	B crimp
Type of contact	Slip-on sleeve
Designation	Crimping position 1
Min. cross section	0.1 mm²
Max. cross section	0.5 mm²
AWG min	26
AWG max	20

Crimping pliers - CRIMPFOX-SC 1,5-M - 1212725

Technical data

General

Designation	Crimping position 2
Min. cross section	0.5 mm ²
Max. cross section	1 mm ²
AWG min	20
AWG max	18
Designation	Crimping position 3
Min. cross section	0.5 mm ²
Max. cross section	1.5 mm ²
AWG min	20
AWG max	16
Weight	560 g
Min. cross section	0.1 mm ²
Max. cross section	1.5 mm ²

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		C-DE.A*77.B.00766
-----	---	-------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>