



These versatile cable ties are available in nine different colors and three different styles to satisfy your application requirements.

TAK-TY® Hook & Loop Cable Ties


Provide an excellent solution for managing Category 5, 5E, 6, and Fiber Optic Network and Telecommunications Cables

- Prevents overtensioning of high performance Category 5, 5E, 6 and fiber optic cables
- Easy to release and reuse
- Ideal for applications requiring frequent cabling moves, adds or changes
- HLSP/HLTP style is U. L. Listed for use in air handling spaces per NEC Section 300-22 (c) and (d) and is UL94V-2 flame rated

Applications:




Category 5, 5E, 6 and fiber optic cables can be managed more effectively with the use of *TAK-TY* Hook & Loop Cable Ties. Use them in the communication closet on both the front and back of racks as shown.



Ties can be used to secure various sizes of cable bundles.




HLT Style can be mounted directly to a rack with a screw.



Wide color choice allows for quick and easy color coding of separate cable bundles.


PANDUIT® TAK-TY® Hook & Loop Cable Ties



HLC Series

Part Number	Length A In. (mm)	Width B In. (mm)	Thickness In. (mm)	Head Width C In. (mm)	Min. Bundle Dia. In. (mm)	Max. Bundle Dia. In. (mm)	Min. Loop Tensile Strength* Lbs. (N)	Packaging**	
								Std. Pkg. Qty.	Std. Ctn. Qty.
Cinch Ties - Cinch ring provides extra strength and bundle tightness									
HLC3S-X0	12.0 (305)	.75 (19)	.10 (2.5)	1.10 (27.9)	2.0 (51)	3.0 (76)	50 (222)	10	100
HLC5S-X0	18.0 (457)	.75 (19)	.10 (2.5)	1.10 (27.9)	3.0 (76)	5.0 (127)		10	100

Pass hook portion through plastic cinch ring. Pull end of tie against ring to tension. Secure hook portion against loop portion of tie body to fasten. Available in black only.





HLT & HLTP Series

Loop Ties - Slot allows for pre-wrapping of bundles									
HLT2I-X0	8.0 (203)	.50 (12.7)	.10 (2.5)	1.00 (25.4)	.25 (6)	1.9 (48)	40 (178)	10	100
HLTP2I-X12								10	100
HLT3I-X0	12.0 (305)	.50 (12.7)	.10 (2.5)	1.00 (25.4)	.25 (6)	3.2 (81)	40 (178)	10	100
HLTP3I-X12								10	100

HLT, HLM and HLS styles are hook on one side and loop on the other so they adhere to themselves. Wrap around bundle and secure end of tie on the body.

HLTP/HLSP style is U. L. Listed for use in air handling spaces per NEC Section 300-22 (c) and (d) and is UL94V-2 flame rated.



HLM, HLS & HLSP Series

Strip Ties - Rolls Perforated in Convenient 6", 12" and 18" strips									
HLS1.5S-X0	6.0 (152)	.75 (19)	.10 (2.5)	—	.25 (6)	1.5 (38)	50 (222)	10	100
HLSP1.5S-X12				—				10	100
HLS3S-X0	12.0 (305)	.75 (19)	.10 (2.5)	—	.25 (6)	3.2 (81)	50 (222)	10	100
HLSP3S-X12				—				10	100
HLS5S-X0	18.0 (457)	.75 (19)	.10 (2.5)	—	.25 (6)	5.0 (127)	50 (222)	10	100
HLSP5S-X12				—				10	100
15' & 75' Rolls - Can be cut to desired length, eliminating waste									
HLM-15R0	180.0 (4572)	.33 (8.4)	.10 (2.5)	—	.25 (6)	Various	18 (80)	1	10
HLM-15R0	180.0 (4572)	.75 (19)	.10 (2.5)	—	.25 (6)	Various	50 (222)	1	10
HLS-75R0	900.0 (22,860)	.75 (19)	.10 (2.5)	—	.25 (6)	Various	50 (222)	1	10

* Minimum 2" overlap required to achieve loop tensile rating (HLC, HLT, HLS, HLM series).

* Minimum 1" overlap required to achieve UL Listed Rated Load (HLSP series). -0 (Black) rated 18 lbs (80N)

* Minimum 1.5" overlap required to achieve UL Listed Rated Load (HLTP series). -0 (Black) rated 18 lbs (80N)

**Order number of pieces required in multiples of packaging quantities.

Color Chart

Color	Part No. Suffix
Black	-0
Red	-2
Orange	-3
Yellow	-4
Green	-5
Blue	-6
Gray	-8
White	-10
Maroon	-12

HLSP/HLTP Series available in black and maroon only.

For a copy of PANDUIT product warranties, log on to www.panduit.com/warranty

For a full line catalog, contact Customer Service and ask for SA101N275C-WC.



PANDUIT CORP.
Tinley Park, Illinois 60477-3091
Customer Service: 800-777-3300
Technical Support: 866-405-6660
Email: ctinfo@panduit.com
Internet: www.panduit.com/eg



Contact your local authorized PANDUIT distributor for pricing. For your local Sales Office call 800-777-3300

PANDUIT CANADA
Markham, Ontario
Phone: 800-777-3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44 208-601-7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: (65) 6379 6700

PANDUIT JAPAN
Tokyo, Japan
Phone (81) (3) 3767-7011

PANDUIT LATIN AMERICA
Jalisco, Mexico
Phone: (52) 3 666-2501

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: (61) 3-9794 9020