




PANDUIT PART NO.	BUNDLE DIA.		A	B	C	D	E	F	G	H	MAX. PANEL THICKNESS	MIN. LOOP TENSILE	CROSS- SECTION	WEIGHT
	MIN. in (mm)	MAX. in (mm)									in (mm)	lbs (N)		100 pcs lbs (g)
PLUP40SE	.06 (1.5)	1.57 (40)	.047 (1.2)	.190 (4.8)	.295 (7.5)	.744 (18.9)	.320 (8.1)	6.97 (177)	.378 (9.6)	.266 (6.8)	.050 (1.3)	50 (222)	STANDARD	.31 (141)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

PLUP40SE
UMBRELLA WINGED PUSH MOUNT CABLE TIEUNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±.1(.25) (.XXX) ±.020(.51)
(.XX) ±.02(.5) ANGLES ± ---UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

8	11/24/04	ERW		CHANGED MIN. LOOP TENSILE TO 50 (222).	27067	8				DRAWN BY BSH	MAT'L: NYLON 6.6	SCALE NONE		
7	11/1/04	JABO	JVL	CHANGED FORMAT FOR CONSISTENCY SEE ECN FOR DETAILS	27067	7	JVL			DATE 11/13/96		DRAWING NO. SS-27067	DWG A	SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D JML				