





### Pan-Ty® Marker and Flag Ties – Nylon 6.6

- Used to fasten and identify bundles at the same time
- One-piece construction for consistent performance and reliability
- Can be marked with Panduit marker pens or custom

imprinted using Panduit Custom Hot Stamping Service (see page P.43)

- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation



|                         | Marker | Length |     | Width |     | Thickness |     | Marker<br>Write-On Area |             | Max.<br>Bundle<br>Dia. |     | Min. Loop<br>Tensile<br>Str. |     | Recommended<br>Installation<br>Tool                                | Std.<br>Pkg.<br>Qty. | Std.<br>Ctn.<br>Qty. |  |  |
|-------------------------|--------|--------|-----|-------|-----|-----------|-----|-------------------------|-------------|------------------------|-----|------------------------------|-----|--------------------------------------------------------------------|----------------------|----------------------|--|--|
| Part Number             | Type   | In.    | mm  | In.   | mm  | In.       | mm  | In.                     | mm          | In.                    | mm  | Lbs.                         | N   |                                                                    |                      |                      |  |  |
| Miniature Cross Section |        |        |     |       |     |           |     |                         |             |                        |     |                              |     |                                                                    |                      |                      |  |  |
| PLF1M-C                 | Flag   | 4.3    | 109 | .098  | 2.5 | .045      | 1.1 | .31 x .75               | 7.9 x 19.1  | .87                    | 22  | 18                           | 80  | GTS, GTSL,<br>GS2B, PTS,<br>PPTS, STS2                             | 100                  | 1000                 |  |  |
| PLF1MA-C                | Flag   | 5.1    | 130 | .098  | 2.5 | .045      | 1.1 | .76 x 1.04              | 19.1 x 26.4 | .87                    | 22  | 18                           | 80  |                                                                    | 100                  | 1000                 |  |  |
| PLF1MB-C                | Flag   | 4.0    | 101 | .098  | 2.5 | .045      | 1.1 | .31 x .92               | 7.9 x 23.4  | .75                    | 19  | 18                           | 80  |                                                                    | 100                  | 1000                 |  |  |
| PLF1MC-M                | Flag   | 4.3    | 109 | .098  | 2.5 | .045      | 1.1 | 2.5                     | 7.9 x 19.1  | .87                    | 22  | 18                           | 80  |                                                                    | 100                  | 1000                 |  |  |
| PLM1M-C                 | Wrap   | 3.9    | 99  | .098  | 2.5 | .035      | .9  | .26 x .95               | 6.6 x 24.1  | .75                    | 19  | 18                           | 80  |                                                                    | 100                  | 1000                 |  |  |
| PLM2M-C                 | Wrap   | 8.0    | 203 | .098  | 2.5 | .035      | .9  | .26 x .95               | 6.6 x 24.1  | 2.00                   | 51  | 18                           | 80  |                                                                    | 100                  | 1000                 |  |  |
| Standard Cross Section  |        |        |     |       |     |           |     |                         |             |                        |     |                              |     |                                                                    |                      |                      |  |  |
| PLM2S-C                 | Wrap   | 7.4    | 188 | .185  | 4.7 | .052      | 1.3 | .44 x .87               | 11.1 x 22.1 | 1.75                   | 45  | 50                           | 222 | GTS, GTSL,<br>GS2B, GTH,<br>GS4H, PTS,<br>PTH, PPTS,<br>STS2, STH2 | 100                  | 1000                 |  |  |
| PLM4S-C                 | Wrap   | 14.6   | 371 | .185  | 4.7 | .052      | 1.3 | .44 x 2.00              | 11.1 x 50.8 | 4.00                   | 102 | 50                           | 222 |                                                                    | 100                  | 1000                 |  |  |
| PL2M2S-L                | Wrap   | 7.4    | 188 | .185  | 4.7 | .052      | 1.3 | .87 x 1.07              | 22.1 x 27.2 | 1.75                   | 45  | 50                           | 222 |                                                                    | 50                   | 500                  |  |  |
| PL3M2S-L                | Wrap   | 7.4    | 188 | .185  | 4.7 | .052      | 1.3 | .87 x 1.79              | 22.1 x 45.5 | 1.75                   | 45  | 50                           | 222 |                                                                    | 50                   | 500                  |  |  |

### Permanent Marking Pens

- Fast drying, permanent ink for identification on marker ties shown above



| Part Number  | Color | Description                          | Std.<br>Pkg.<br>Qty. | Std.<br>Ctn.<br>Qty. |
|--------------|-------|--------------------------------------|----------------------|----------------------|
| <b>PX-0</b>  | Black | Permanent marking pen – regular tip. | 12                   | 144                  |
| <b>PX-2</b>  | Red   | Permanent marking pen – regular tip. | 12                   | 144                  |
| <b>PFX-0</b> | Black | Permanent marking pen – fine tip.    | 12                   | 144                  |
| <b>PFX-2</b> | Red   | Permanent marking pen – fine tip.    | 12                   | 144                  |