






- NOTES
1. MATERIAL & COLOR : SEE TABLE
 2. MATCHED HOUSING : 35180-060*
 3. APPLICABLE TERMINAL : 35748-0*10
 4. APPLICABLE T.P.A : 35182-019*

NO	PRODUCT		MATERIAL	
	PART NO	MATERIAL NO	COLOR	DESCRIPTION
1	35181-0220	351810220	NATURAL	PBT (UL94V-0)
2	35181-0229	351810229	NATURAL	PBT/PC(UL94V-0)

REVISED	EC NO: KOR2008-0048	2007/09/10
DRWN: JHPARK01	2007/09/10	
CHKD: WY. YANG	2007/09/10	
APPR: YUNSIKKIM	2007/09/10	
REV	DESCRIPTION	

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± ---
1 PLACE	± 0.3	± ---
ANGULAR ± 1 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	
MM ONLY	
DRAWN BY	DATE
JS. KANG	
CHECKED BY	DATE
APPROVED BY	DATE
MATERIAL NO.	
SIZE	A3

SCALE 3:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
TITLE . 070 MULTI W/W CONN FEMALE HSG-2P(C)		
MOLEX INCORPORATED		
DOCUMENT NO. SD-35181-022*		SHEET NO. 1 OF 01
CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		